


CABLE OUTLET POSITION 3

1:2




THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZÜGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (Z.B. BIEGESCHLAPPE KABEL) KÖNNEN DIE DELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITÄT NICHT BEEINTRÄCHTIGT IST.


REVISIONS ÄNDERUNGEN				
P.	LTR.	DESCRIPTION BESCHREIBUNG	DATE	DWN APVD
F		NOTES UPDATED, COMPONENT REVISED	16 JUN 2016	JM JJ
G		COMPONENT (CABLE, 2 x 0.75 mm ²) REVISED	27 NOV 2018	JM JJ
H		COMPONENT REVISED	05 OCT 2020	OS JJ

INTERFACE VIEW
Schnittstellen Ansicht



LENGTH SCHEDULE:
Laengentabelle:


TE PART NO.	REV.	LENGTH L (mm)	TOL.	CABLE OUTLET POSITION
2-2208877-1	H	1000	+30	Position 3
2-2208877-5	H	5000	+60	



WIRING SCHEDULE:
Belegungsplan:

CAVITY-NO.	IDENTIFICATION	WIRE COLOUR	WIRE SECTION
1	L1	RED	4mm ² (ITEM 12)
2	L2/N	BROWN	4mm ² (ITEM 12)
3	GROUND/EARTH	BROWN	4mm ² (ITEM 13)
4	CP	BROWN/WHITE	0.75mm ² (ITEM 14)
5	CS	WHITE	0.75mm ² (ITEM 14)

5 LABEL LEGEND:
Label Beschriftung:



NOTES

- PACKAGING ACCORDING SPECIFICATION V2208877.
- STRIPPED ONLY OUTER JACKET AND BRAID. ELECTRICAL TESTING IS ACCORDING APPLICATION SPECIFICATION.
- APPLICATION SPECIFICATION: 114-94163-1 CHARGE INLET IEC 62196-2 TYPE 1.
- CUTTING LENGTHS TO BE FIXED BY MANUFACTURING.
- MANUFACTURING CODE: TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY), TO BE PRINTED ON LABEL (ITEM 17). LABEL TO BE APPLIED TO THE CABLE AFTER SUCCESSFUL ELECTRICAL TEST.

1	RESISTOR, 2K7, 1%	18
2	CONTACT KIT, R5, INLET TYPE 1, PLATED	17
3	CAB TIE, CLIP, HELL, T18R-HR-N46	16
1	LABEL, HELL	15
see table	CABLE, 2 x 0.75 mm ² , BLACK	14
see table	CABLE, 4 mm ² , BROWN	13
see table	CABLE 2 x 4.0 mm ² , BRAID	12
5	O-RING, 3 x 1.5	11
2	PIN DIA 1.5, CP/CS	10
1	PIN DIA 2.8, PE	9
2	PIN DIA 3.6, L/N, ASSY	8
3	SELF TAPPING SCREW	7
2	FAMILY SEAL, MIXED, Vers.1	6
1	INSULATION COVER, TE, COVER INLET	5
1	CABLE FIXATION, TE, COVER INLET	4
1	ACTUATOR, LOCKING UNIT, ASSY	3
1	2. LOCK, TE, IEC62196-2 TYPE 1	2
1	5 POS, MIXED, HSG, IEC62196-2 TYPE 1	1
QTY X-Y	DESCRIPTION	ITEM NO.
-	WEIGHT OF ASSY NO. [g]	-

TOLERANCING EN ISO 8015 TOLERIERUNG EN ISO 8015		DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).		DWN M. Zelch 01JUL2013		APVD M. Folk 03JUL2013		NAME HV, CHARGE INLET TYPE 1, HYB ASSY, 4 sqmm		SIZE A		CAGE CODE 00779		DRAWING NO. ©=2208877		RESTRICTED TO NUR FÜR	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DIMENSIONS: MASSENHEITEN: [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		PRODUCT SPEC PRODUKTSPEZ.		APPLICATION SPEC VERARBEITUNGSSPEZ.		SCALE MASSSTAB		SHEET BLATT		OF VON		REV H	
0 PLC ±		1 PLC ±		2 PLC ±		3 PLC ±		4 PLC ±		ANGLES/WINKEL		WEIGHT GEWICHT		CUSTOMER DRAWING		KUNDENZEICHNUNG	
FINISH/BOBERFLÄCHE/FARBE		MATERIAL		SCALE MASSSTAB		SHEET BLATT		OF VON		REV H							