
2379397-5 ✔ ACTIVE

TE Internal #: 2379397-5

Mini Cool Edge I/O (MCIO), Cable Plug Assembly, Vertical, Cable-to-Board, 74 Position, Surface Mount, Internal I/O Connectors

View on TE.com >

Connectors > PCB Connectors > Internal I/O Connectors







Internal I/O Connector Type: **Mini Cool Edge I/O (MCIO)**

Connector Mates With: **Cable Plug Assembly**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **74**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Internal I/O Connector Type	Mini Cool Edge I/O (MCIO)
Connector Mates With	Cable Plug Assembly
Connector System	Cable-to-Board

Configuration Features

Number of Rows	2
PCB Mount Orientation	Vertical
Number of Positions	74

Contact Features

PCB Contact Termination Area Plating Material	Tin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1 A
Contact Mating Area Plating Material Thickness	.076 µm[30 µin]

Termination Features

Termination Method to PCB	Surface Mount

Mechanical Attachment

Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	.6 mm[.023 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Operation/Application

Circuit Application	Signal

Industry Standards

Industry Standard	SFF-TA-1016

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2366780-1
CA, MCIO x8 STR-RA push 30AWG 0.5 m

TE Part # 2366550-2
CA, MCIO x8 Lateral push 30AWG 1.0 m

TE Part # 2366780-2
CA, MCIO x8 STR-RA push 30AWG 1.0 m



TE Part # 2366550-1
CA, MCIO x8 Lateral push 30AWG 0.5 m

Customers Also Bought




TE Part #2143451-1
SFP+ 1X2 Assy, Sldr Tail, Tray


TE Part #3-2204805-8
ELCON MICRO,HDR,VERTICAL DIP W /CAP,8P



TE Part #1-2328461-1
280 POS., CONNECTOR ASSEMBLY, SLIVER 2.0



TE Part #5-2337939-8
PCIE GEN4 CON,SMT,164POS,30u", MYLAR,HT



TE Part #6-2340321-4
ASSY STRADDLE MOUNT 168P 076 SLIVER 2.0




TE Part #5-2349820-7
PCIEG4,SMT,V,98P,30u,ML,HT,OEW



TE Part #1-2351052-2
LGA4677 E1B ASSY



TE Part #1-2351052-5
LGA4677 E1A ASSY



TE Part #2358256-1
SBCE, 2X25P

TE Part #2369957-5
SLIM SAS 4X VT 100OHM

Documents

Product Drawings

MCIO INTERGRATED CONN, V/T,8X, SMT TYPE

English

CAD Files

Customer View Model

ENG_CVM_CVM_2379397-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2379397-5_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2379397-5_A.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English