



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **3200 – 8300 CMA**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Terminal Orientation: **Flag**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Tab-Lok
Barrel Type	Open

Termination Features



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Wire Size	3200 – 8300 CMA

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Packaging Features

Packaging Quantity	3500
Packaging Method	Reel/Carton

Other

Line	FASTON .250
------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 42474-4
250 FASTON TAB 18-14 AWG TPBR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(117)

Insulation Boots & Sleeves(16)

Magnet Wire Terminals(1)

PCB Terminals(131)


Quick Disconnects(404)

Splices(4)

Customers Also Bought



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #9437153001
100G0111-2.50-6



TE Part #41531
250 FASTON FLAG REC 18-12 AWG
BR



TE Part #62718-2
250 FASTON FLAG REC 22-18 AWG
TPBR



TE Part #62811-2
250 FASTON FLAG REC 18-14 AWG
TPBR




TE Part #62814-1
250 FASTON FLAG REC 22-18 AWG
BR




TE Part #165075
P.G. WIRE PIN 16-14



TE Part #170891-2
250 FASTON HSG., FLAG, REC.,
NATURAL



TE Part #284391-2
TERMI-BLOK PCB SIDE ENTRY STAC



TE Part #5-535542-2
04 MODIV VRT DR CE 100/130

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2238206-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2238206-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2238206-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON TERMINALS (INSULATED AND UNINSULATED) - FULL CATALOG

English

Product Specifications



Application Specification

English