



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP ECN-22-147784	08APR2022	JZ	WKH



- NOTES:
- PARTS AND PROCESSES RoHS COMPLIANT PER TE CONNECTIVITY STANDARD TEC-138-702.
  - PRODUCT RATING:  
CHARACTERISTIC IMPEDANCE: 50 OHMS Normal  
FREQUENCY RANGE: DC TO 9GHz
  - CABLE ASSEMBLY TO BE 100% OPEN & SHORT TESTED
  - UMCC GEN1 CAN MATE WITH I-PEX MHF1 SERIES AND HIROSE U.FL SERIES

1-2411050-0	500±5
2411050-9	450±5
2411050-8	400±5
2411050-7	350±5
2411050-6	300±5
2411050-5	250±5
2411050-4	200±3
2411050-3	150±3
2411050-2	100±3
2411050-1	50±3
P/N	LENGTH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JZ	01APR2022			
		CHK	WKH	01APR2022			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME RF CA, UMCC GEN1- PIGTAIL WITH 1.37MM CABLE		
		0 PLC	±-		PRODUCT SPEC 108-2231		
		1 PLC	±0.1		APPLICATION SPEC -		
		2 PLC	±0.01		SIZE A3		
		3 PLC	±0.001		CAGE CODE 00779		
		4 PLC	±0.0001		DRAWING NO G-2411050		
		ANGLES	±-		RESTRICTED TO -		
MATERIAL -		FINISH -			WEIGHT -		
					CUSTOMER DRAWING		
					SCALE 8:1		
					SHEET 1 OF 1		
					REV A		