



Switches > Push Button Switches > Emergency Stop Switches: 22mm Mounting Hole, Pushbutton



Configuration (Pole-Throw): **Single Pole - Single Throw**
Push Button Switch Product Type: **Emergency Stop Switch**
Number of Actuators: **Single**
Actuator Profile: **Extended**
Bushing Style: **Threaded**

[All Emergency Stop Switches: 22mm Mounting Hole, Pushbutton \(54\)](#)

Features

Product Type Features

Switch Connection Type	Screw Terminal
Push Button Switch Product Type	Emergency Stop Switch
Illuminated	With
Actuator Style	Top Actuator

Configuration Features

Panel Cutout Size	22.3 mm[0.88 in]
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	With
Switch Feedback Type	Tactile & Auditory
Operating Function	Maintained, NC

Electrical Characteristics

--	--



Contact Current Rating	10 A
------------------------	------

Operating Voltage Range	120 VAC
-------------------------	---------

Body Features

Case Material	Polyamide
---------------	-----------

Sealing Method	Rubber O-Ring
----------------	---------------

Actuator Material	Polyamide
-------------------	-----------

Product Orientation	Vertical
---------------------	----------

Actuator Force	4079 g[144 oz]
----------------	----------------

Actuator Profile	Extended
------------------	----------

Bushing Style	Threaded
---------------	----------

Bushing Thread Size	M22 x 1
---------------------	---------

Actuator Color	Red
----------------	-----

Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------

Mechanical Attachment

Attachment Method	Screw-On
-------------------	----------

Dimensions

Bushing Length	45.6 mm[1.8 in]
----------------	-----------------

Bushing Diameter	22 mm[.87 in]
------------------	---------------

Actuator Length	33 mm[1.3 in]
-----------------	---------------

Operation/Application

Actuator Total Travel	8 mm[.3 in]
-----------------------	-------------

Industry Standards

IP Rating	IP65
-----------	------

Packaging Features

Packaging Method	Bulk
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted
---	----------------------------



	Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-W06-P2240
Emergency Stop Switches: 22mm
Mounting Hole, Pushbutton

Also in the Series | [ALCOSWITCH PBES22](#)



Emergency Stop Switches(54)



Push Button Switches(54)

Customers Also Bought



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #CAT-D48-ST273
DEUTSCH Connector Solid Contacts



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

Product Drawings

PBES22 40 INCA 6V AC/DC 6.3V 1W 000 NC

English

CAD Files

Customer View Model

ENG_CVM_CVM_2416049-5_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2416049-5_A1.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2416049-5_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

ALCOSWITCH_PUSHBUTTON_22mm_EMERGENCY_STOP_SWITCH

English