



Gasket Type: **EMI Connector Gasket**

Finished Type: **Conductive Sheet**

Binding Material: **Silicone**

Filler Material: **Silver Plated Aluminum (Ag/Al)**

Gasket Shape: **Rectangular**

[All Standard MIL-DTL-5015 Connector Gaskets \(60\)](#)

## Features

### Product Type Features

Finished Type	Conductive Sheet
Binding Material	Silicone
Filler Material	Silver Plated Aluminum (Ag/Al)

### Electrical Characteristics

Resistance to Petroleum	No
Volume Resistivity (Max)	.008 Ω.cm

### Body Features

Gasket Type	EMI Connector Gasket
Gasket Shape	Rectangular

### Dimensions

Product Thickness	.8 mm [.031 in]
Product Width	50.8 mm [2 in]

### Usage Conditions

--	--



Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

**Operation/Application**

Compatible With Connector Shell Size	28
--------------------------------------	----

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: DCP (.22% in Component) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**




TE Part # CAT-EMIG-0005  
Standard MIL-DTL-5015 Connector Gaskets



TE Part # 2488540-1  
Conn G SNA 5015 Shell 28 10pk



TE Part # 2488571-1  
Conn G SNA 5015 Shell 28 1pk



TE Part # 2488556-1  
Conn G FNA 5015 Shell 28 10pk



TE Part # 2488586-1  
Conn G FNA 5015 Shell 28 1pk

Also in the Series | **Kemtron 92 Series**



EMI Connector Gaskets(120)



Medical EMI Gaskets(120)

Documents

Product Drawings

Conn G SSA 5015 Shell 28

English

CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_2423984-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2423984-1\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2423984-1\\_A.2d\\_dxf.zip](#)

English

3D PDF

3D



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

[performance-materials-brochure](#)

English

[Connector Gaskets for RFI/EMI Shielding](#)

English

---

## Product Specifications

[Application Specification](#)

English