



EMI & EMC Solutions > EMI Shielding > EMI Connector Gaskets > D-Sub Conn Gaskets for RFI/EMI Shielding



Gasket Type: **EMI Connector Gasket**
Filler Material: **Nickel Plated Graphite (Ni/C)**
Product Thickness: **.8 mm [.031 in]**
Product Width: **35.8 mm [1.409 in]**
Operating Temperature Range: **-55 – 160 °C [-67 – 320 °F]**

[All D-Sub Conn Gaskets for RFI/EMI Shielding \(40\)](#)

Features

Product Type Features

Filler Material	Nickel Plated Graphite (Ni/C)
-----------------	-------------------------------

Configuration Features

Number of Positions	9
---------------------	---

Electrical Characteristics

Resistance to Petroleum	Yes
Volume Resistivity (Max)	.05 Ω/cm

Body Features

Gasket Type	EMI Connector Gasket
-------------	----------------------

Dimensions

Product Thickness	.8 mm[.031 in]
Product Width	35.8 mm[1.409 in]

Usage Conditions

--	--



Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: DCP (.33% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2488694-1
Conn G FNA 0.8mm D-Sub 9 Pin 10pk



TE Part # CAT-EMIG-0009
D-Sub Conn Gaskets for RFI/EMI Shielding




TE Part # 2488684-1
Conn G SNA 0.8mm D-Sub 9 Pin 10pk





TE Part # 2488714-1
Conn G FNA 0.8mm D-Sub 9 Pin 1pk



Also in the Series | **Kemtron 95 Series**



Customers Also Bought





Documents

Product Drawings

Conn G FNG 0.8mm D-Sub 9 Pin

English

CAD Files

Customer View Model

ENG_CVM_CVM_2430147-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2430147-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2430147-1_A.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

performance-materials-brochure

English

Connector Gaskets for RFI/EMI Shielding

English

Product Specifications

Application Specification

English