

2303237-4 ✓ ACTIVE



## AMP+ | Charging Inlets

TE Internal #: 2303237-4

2 Position, Orange, Cover, PA 6, 180 ° Cable Exit, -40 – 85 °C [-40 – 185 °F], Charging Inlets

[View on TE.com >](#)

Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 2

Primary Product Color: **Orange**

Protection & Strain Relief Accessory Type: **Cover**

Primary Product Material: **PA 6**

Cable Exit Angle: **180 °**

### Features

#### Product Type Features

Sealable	Yes
Protection & Strain Relief Accessory Type	Cover

#### Configuration Features

Number of Positions	2
---------------------	---

#### Body Features

Primary Product Color	Orange
Primary Product Material	PA 6
Cable Exit Angle	180 °

#### Mechanical Attachment

Strain Relief	Without
---------------	---------

#### Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts

<p>TE Part # 2481865-1 <a href="#">CHARGE INLET ASSY,EK0 CCST1</a></p>	<p>TE Part # 2303200-1 <a href="#">CABLE EXIT, RECT, COMBO, LEFT</a></p>	 <p>TE Part # 1-2303200-2 <a href="#">CABLE EXIT, RECT, COMBO RIGHT</a></p>
--	--	--

## Also in the Series | [Charging Inlets](#)




Automotive Connector Caps & Covers (60)



Automotive Connector Locks & Position Assurance(3)




Automotive E-Mobility Connector Housings(1)



Automotive Housings(31)



Automotive Seals & Cavity Plugs(5)



Automotive Terminals(4)



Electric, Hybrid & Fuel Cell Cable Assemblies(104)



Other Automotive Connector Accessories(2)

## Customers Also Bought



TE Part #2120571-1  
SEALING



TE Part #2141404-1  
20POS,NANOMQS,REC HSG,CODE A



TE Part #2293269-3  
DIA 6MM,PIN TERMINAL




TE Part #2293270-4  
PIN DIA 6.0,RIGID,POWER PE



TE Part #5-2296057-3  
COVER, CABLE SEAL, AC



TE Part #1-2303200-2  
CABLE EXIT, RECT, COMBO RIGHT



TE Part #2331969-1  
BLIND PLUG, DC, COMBO2

## Documents

### Product Drawings

[COVER, CABLE SEAL, COMBO DC](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2303237-4\\_A.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2303237-4\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2303237-4\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English