




BNC

TE Internal #: 2476057-1
BNC Connector, Jack, 75 ohm, Bayonet, 2 GHz, Cable-to-Board, 1
Position, Printed Circuit Board, Board Mount, -65 – 165 °C [-85 –
329 °F], Brass, BNC

[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **BNC**
RF Connector Style: **Jack**
RF Connector Mated Outer Diameter (Approximate): **17.45 mm [.687 in]**
Impedance: **75 Ω**
RF Connector Coupling Mechanism: **Bayonet**

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Body Underplating Material	Copper
Body Material	Brass



Body Material Finish	Plated
Body Plating Material	Nickel

Contact Features

Outer Contact Plating Material	Nickel (Ni)
RF Connector Contact Configuration	Captivated
RF Connector Center Contact Plating Thickness	.076 µm[3 µin]
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Beryllium Copper

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	6.35 mm[.25 in]

Mechanical Attachment

RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Product Length	22.23 mm[.875 in]
Profile Height from PCB	6.35 mm[.25 in]
RF Connector Mated Outer Diameter (Approximate)	17.45 mm[.687 in]

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
Operating Frequency Range	2 GHz

Packaging Features

Packaging Quantity	60
Packaging Method	Tray

Other

Dielectric Material	Polytetrafluoroethylene (PTFE)
---------------------	--------------------------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (3.15% in M-43353-9) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 2484792-1
BNC Plug Str RG174 188A 316 4 GHz 50 Ohm

TE Part # 2485916-1
BNC Plug St Crimp Belden 8218 4G 75 Ohm

TE Part # 2485918-1
BNC Plug St Crimp RG59 20AWG 2GHz 75 Ohm

TE Part # 2486506-1
BNC M Str Crimp RG-161, 179, 187 75 Ohm



TE Part # 1-1337429-0
BNC Str Plg Hex 75Ohm Silver Pltd
RG59B/

TE Part # 2476195-1
BNC Plug Str Crimp Rg58 Lmr195 50
Ohm

Also in the Series | BNC

BNC RF Connectors(167)

Customers Also Bought

TE Part #66460-9
PIN,.062 DIA,.025 SQ POST,LP

TE Part #535032-5
096 EURO TYPE C RECEPT AP ASSY

TE Part #3-641534-3
03P MTA100 CONN ASSY LF

TE Part #1379659-5
8W PLUG HOUSING ASSY NATU

TE Part #3-1630186-6
HSA50 14R 5%

TE Part #2-5174339-5
AMPLIMITE CAP HEADER

TE Part #5745072-4
HD-20 PLUG 15P VERT FFSCRLK

TE Part #1-5102156-0
A/L UNIV HDR 50P VERT

TE Part #103670-7
08 MTE HDR SRST LATCH W/HLDWN

TE Part #1-103908-5
16 MTE HDR SRST LATCH W/HLDWN



Documents

Product Drawings

BNC Jack Str PCB Mnt Thru Hole 75 Ohm

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2476057-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2476057-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2476057-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

PCB Decoupled BNC Straight & Right Angle Jacks

English

Product Specification

English