




Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers > LEAVYSEAL Connector Backshells



Number of Positions: 25

Primary Product Color: Black

Protection & Strain Relief Accessory Type: Cover - Cable Exit

Primary Product Material: PA GF

Cable Exit Angle: 90°

[All LEAVYSEAL Connector Backshells \(25\)](#)

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
---	--------------------

Configuration Features

Number of Positions	25
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PA GF
Cable Exit Angle	90°

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	26 mm[1.024 in]
--	-----------------

Usage Conditions

--	--



Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
Packaging Quantity	300

Other

Serviceable	Yes
-------------	-----

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-L489-CH8172
[LEAVYSEAL Connector Housings](#)

Also in the Series | **LEAVYSEAL**




[Automotive Connector Caps & Covers \(25\)](#)



[Automotive Housings\(117\)](#)

Customers Also Bought



TE Part #892275J001
[V2-16.0-0-FSP-SM](#)




TE Part #2-178129-6
[6-P DYNAMIC PLUG-H D3200 5.08](#)



TE Part #964267-2
[TAB A 1.6x0.6 CONTACT CF SRC Sn](#)



TE Part #CAT-L489-CH8172
[LEAVYSEAL Connector Housings](#)



TE Part #1747418-2
[DYNAMIC D4200 REC CONT M](#)



TE Part #1827540-1
[DYNAMIC D-2600 HYBRID REC HSG 48P](#)

Documents

Product Drawings
[COVER,90,25/29POS REC HSG](#)

English

CAD Files
[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_2327810-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2327810-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2327810-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LEAVYSEAL CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

German