




Terminals & Splices > Splices



Splice Type: **Pigtail Splice**

Wire Size: **.8 – 2.5 mm²**

Sealable: **No**

Splice Capacity: **3**

Features

Product Type Features

Splice Type	Pigtail Splice
Sealable	No
Compatible With Discrete Wire Type	Magnet Wire, Solid

Configuration Features

Strip Orientation	End Feed
Splice Capacity	3
Number of Serrations	7

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Body Features

Product Weight	.272 g
Splice Features	Serrated

Contact Features

Terminal Plating Material	Tin
---------------------------	-----



Contact Base Material	Brass
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	1500 – 5000 CMA
Barrel Inside Diameter	1.66 mm[.065 in]
Terminal Material Thickness	.5 mm[.02 in]
Product Length	5.72 mm[.225 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	30000
Packaging Method	Strip

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-141175-3
SPICE AMPLIVAR



TE Part # 1-141175-2
AMPLIVAR SPL 5 SERR



TE Part # 1742324-2
AMVAR STAKE SPLICE 020TPBR




TE Part # 7-2150009-7
OCEAN_2.0_SPARE_PART_KIT-110F




TE Part # 2150009-2
OCEAN_2.0_Applicator-E-110F-SEA

Also in the Series | AMPLIVAR



Crimp Wire Pins, Tabs & Ferrules(4)



Magnet Wire Terminals(4)



PCB Terminals(1)



Quick Disconnects(39)




Ring Terminals(28)



Splices(69)

Customers Also Bought




TE Part #62000-2
SPLICE AMVAR 600-3000 020TPBR



TE Part #140814-2
250 FASTON,TAB,TPBR



TE Part #324615
TERMINAL,PIDG R 12-10 5/8




TE Part #350687-1
UMNL SPLIT PIN PTPBR



TE Part #1-480707-0
09P UMNL CAP HSG NATL




TE Part #485043-2
SPLICE 4000-9000 .020 TPBR




TE Part #737060-2
AMPLIVAR SPL 5 SERR W/INS SUP



TE Part #776433-2
AS16,PLUG ASSY,ST,06P,N SEAL, CODE B



TE Part #280005-2
AMPLIVAR SPLICE



TE Part #2176110-1
3W SM M/OX 5% 12K STEEL LEADS

Documents

Product Drawings

AMPLIV 1500 5000

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_280002-2_U.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_280002-2_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280002-2_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Magnet Wire Terminals & Splices

English

Product Specifications

[Application Specification](#)

English

AMPLIVAR 7 Serration Pigtail Splice

English