




Fiber Optics > Fiber Optic Connectors > Backplane Fiber Optics



Fiber Optic Product Type: MT Ferrule Kit Without Pins

Fiber Optic Connector Type: VITA 66

Number of Fibers: 12

Features

Product Type Features

Fiber Optic Mode	Multimode
Fiber Optic Product Type	MT Ferrule Kit Without Pins
Fiber Optic Connector Type	VITA 66

Configuration Features

Number of Fibers	12
------------------	----

Body Features

Primary Product Material	Aluminum
--------------------------	----------

Dimensions

Compatible Fiber Diameter	125 µm
---------------------------	--------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted



	Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2828383-1
CONN KIT,VITA66.4-DERIV,RCPT,
DUAL-CAVITY




TE Part # 2356183-1
Conn Kit,VITA66.4-Deriv,Rcpt,Dual-
Cavity


Customers Also Bought



TE Part #5052932059
RNF-100-1/16-9-STK



TE Part #216026-007
55A0111-24-9



TE Part #1SNA115486R0300
MA2.5/5



TE Part #1410946-1
MULTI-GIG SOC. CAP SCREW,
CUSTOMIZED HDW






TE Part #3-1625890-3
2W SM M/OX 5% 22R



TE Part #5-1625892-4
3W SM M/OX 5% 47R



TE Part #1-2176582-1
RLC73PD 2B R768 1% 5K RL



TE Part #2359410-1
ASSEMBLY, HYBRID NanoRF/MT DC
MODULE



TE Part #1515740-1
INSERT ASSY, 4 X 1310/1550 SM, JR



TE Part #1515867-1
PROTECTIVE CAP, PLUG, PRO BEAM
JR.

Documents

Product Drawings

MT FERRULE KIT, MM, 12-F, W/O PINS, RCPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2828413-1_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2828413-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2828413-1_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English