

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

**P/N 2349371-2 AS SHOWN
(HVIL: MQS CAVITIES)**

NOTES:

- RECEPTACLE HOUSING IS SUITABLE FOR TE CONNECTIVITY ASSEMBLY PN 1-2349364-0
- MATERIAL: PA66 GF BLACK COLOUR
- WEIGHT: 9.1 GRAM
- SUITABLE FOR FOLLOWING CONTACTS:

CAVITY Nr.	1 - 5	6 - 7
FEMALE CONTACT	AMP MCP 6.3/4.8	MQS
MAX. WIRE SIZE RANGE [mm ²]	6 (ISO 6722-THIN WALL)	0.5 (FCA SP.91107/43)
TE CONNECTIVITY PN	2-1241408-3	5-963715-6

NOTES:

- RECEPTACLE HOUSING IS SUITABLE FOR TE CONNECTIVITY ASSEMBLY PN 2349364-1
- MATERIAL: PA66 GF BLACK COLOUR
- WEIGHT: 8.9 GRAM
- CONDITION ON DELIVERY: SECONDARY LOCKING DEVICE IN PRELOCKING POSITION - IF IN ENDLOCKING POSITION AFTER TRANSPORTATION, PLEASE RELOCK IN ACCORDANCE TO APPLICATION SPECIFICATION

5 SUITABLE FOR FOLLOWING CONTACTS:

CAVITY Nr.	1 - 5	6 - 7
FEMALE CONTACT	AMP MCP 6.3/4.8	MCON-1.2 LL
MAX. WIRE SIZE RANGE [mm ²]	6 (ISO 6722-THIN WALL)	0.5 (FCA SP.91107/43)
TE CONNECTIVITY PN	2-1241408-3	7-1452656-3

**P/N 2349371-1 AS SHOWN
(HVIL: MCON CAVITIES)**

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		FIRST ISSUE	24OCT2019	M.P.	A.G.
B		UPDATED	23JAN2020	M.P.	A.G.

2349371-2	5+2 POS. MCP 6.3/4.8K, MQS. REC HSG	9.60	BLACK
2349371-1	5+2 POS. MCP 6.3/4.8K, MCON. REC HSG	9.60	BLACK
TE-PART-NO.	DESCRIPTION	WEIGHT (g)	COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. BARBON	01MAR2019	TE Connectivity	
DIMENSIONS: mm		CHK -	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. GENIA	01MAR2019	NAME	
0 PLC ±0.5		PRODUCT SPEC		RECEPTACLE HOUSING, HV CONNECTOR, 5+2 POS.	
1 PLC ±0.3		108-		SIZE	
2 PLC ±0.3		APPLICATION SPEC		CAGE CODE	
3 PLC ±		114-20233		DRAWING NO	
4 PLC ±		WEIGHT		RESTRICTED TO	
ANGLES ±1°		CUSTOMER DRAWING		SCALE	
FINISH		A2		SHEET	
SEE NOTES		2:1		1 OF 1	
		REV		B	

1471-9 (3/13)