



Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: **Tab Terminal**
Mating Tab Width: **31.9 mm [1.26 in]**
Mating Tab Thickness: **3.5 mm [.138 in]**
Terminal Material Thickness: **3.5 mm [.138 in]**
Terminal Plating Material: **Silver**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
------------------------------------	----------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Crimp Wire Terminal Type	Tab Terminal
Mating Tab Width	31.9 mm[1.26 in]
Mating Tab Thickness	3.5 mm[.138 in]
Terminal Plating Material	Silver
Contact Shape & Form	Stack Through

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Terminal Material Thickness	3.5 mm[.138 in]
Overall Product Length	57.8 mm[2.28 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2840393-1
HC-STAK 25,TERMINAL

Also in the Series | HC-STAK 35




Crimp Wire Pins, Tabs & Ferrules(1)

Customers Also Bought



TE Part #DT04-08PA-EP04
REC, 8P, GRY, N, CAP, A



TE Part #2349369-1
5POS,HVA630,180DEG,COVER ASSY, SINGLECORE



TE Part #2381326-2
COLLET,1POS,HC-STAK 35,95MM2



TE Part #2385150-2
CU ALLOY,INNER FERRULE,HC-STAK 35,95MM2



TE Part #2385151-2
CU ALLOY,OUTER FERRULE,HC-STAK 35,95MM2




TE Part #2385152-2
SWS,HC-STAK 35,CABLE SEAL,1POS, 95MM2



TE Part #2385722-2
2POS,HC-STAK 35,TAB OUTER HSG ASSY,COD B



TE Part #348462-1
ECON 3 HC PLUG SILICONE



TE Part #0938973001
62E0119-1.00-9(B01)



TE Part #1-342756-0
6 WAY POS. MATE RECEPT. HSG.W



Documents

Product Drawings

HC-STAK 35,TERMINAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2840535-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2840535-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2840535-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English