



THERMAL BRIDGE TECHNOLOGY

FOR INPUT/OUTPUT (I/O) APPLICATIONS

BENEFITS

- 2x better thermal resistance
- Better reliability and durability
- Improved application serviceability

APPLICATIONS

- High performance computing (HPC)
- Ethernet switches
- 5G/wireless
- Servers
- Ethernet SP routing


Thermal bridge technology is the latest thermal innovation from TE Connectivity (TE) and provides up to 2x better thermal resistance over traditional thermal technologies such as gap pads or thermal pads. This solution was developed as our customers seek ways to dissipate more heat associated with increasing power requirements, specifically in applications with restricted airflow, liquid cooling or cold plate applications.

In addition to superior thermal performance over comparable thermal solutions in the market, thermal bridge technology provides better reliability thanks to an elastic compression design that is resistant to set and relaxation over time. This helps ensure consistent, longer-lasting performance and reduces component replacement during servicing.

te.com/thermalbridge

HOW THERMAL BRIDGE WORKS

- An interleaved series of highly parallel plates allows heat to pass from the I/O module to the cooling area
- Integrated mechanical springs provide interface force and 1.0 mm of compression travel
- Near-zero plate gap for compressibility and thermal transfer
- Comes pre-assembled on I/O cage
- Interface may be greased (optional)



Technical Features & Benefits


- Spring loaded bridge offers 1.0mm (typical) of z-axis compression
- Individual plate actuation allows for surface conformability in the x-axis
- Dual-spring design allows for tilt conformability in the y-axis
- At 3 points of contact per plate, a typical bridge will have 150+ points of contact to adjacent surface
- Dry interface resistance 20-40% lower than most traditional riding heatsinks

Product Specification






- [Document #: 108-130042](#)

Application Specification

- View specification documents for each individual part number (see page 3)



AVAILABLE CAGE ASSEMBLIES WITH THERMAL BRIDGE

TE Part Number	Form Factor	Configuration	Image
2358986-1	SFP+	1x1	
2354751-1	QSFP-DD	1x1	
2359309-1	QSFP28	1x1	
2354935-1	QSFP28	1x4	
2355519-1	QSFP28	1x6	

Contact TE for custom design options.

TE Technical Support Center

USA:	1.800.522.6752
Canada:	1.905.475.6222
Mexico:	52.0.55.1106.0800
Latin/S. America:	54.0.11.4733.2200
Germany:	49.0.6251.133.1999
UK:	44.0.800.267666
France:	33.0.1.3420.8686
Netherlands:	31.0.73.6246.999
China:	86.0.400.820.6015

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks owned or licensed by the TE Connectivity family of companies.

All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2019 TE Connectivity Ltd. family of companies All Rights Reserved.