




AMP CT

TE Internal #: 292175-9  
PCB Mount Header, Vertical, Wire-to-Board, 9 Position, 2 mm [.078 in] Centerline, Partially Shrouded, Tin (Sn), Surface Mount, Power & Signal, AMP CT

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles > CT Box Header SMT: Vert, Shrouded



PCB Connector Type: **PCB Mount Header**  
PCB Mount Orientation: **Vertical**  
Connector System: **Wire-to-Board**  
Number of Positions: **9**  
Centerline (Pitch): **2 mm [.078 in]**

[All CT Box Header SMT: Vert, Shrouded \(34\)](#)

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| PCB Connector Type                | PCB Mount Header      |
| Connector System                  | Wire-to-Board         |
| Header Type                       | Partially Shrouded    |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |
| Connector Product Type            | Connector Assembly    |

Configuration Features

|                       |          |
|-----------------------|----------|
| PCB Mount Orientation | Vertical |
| Number of Positions   | 9        |
| Number of Rows        | 1        |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 125 VDC |
|-------------------|---------|



Body Features

|                       |         |
|-----------------------|---------|
| Primary Product Color | Natural |
|-----------------------|---------|

Contact Features

|                                                         |                             |
|---------------------------------------------------------|-----------------------------|
| Mating Pin Diameter                                     | .6 mm[.024 in]              |
| PCB Contact Termination Area Plating Material Thickness | 1 – 2 µm[39.37 – 78.73 µin] |
| Contact Shape & Form                                    | Round                       |
| Contact Layout                                          | Inline                      |
| Contact Mating Area Length                              | 4.5 mm[.177 in]             |
| Contact Base Material                                   | Brass                       |
| Contact Mating Area Plating Material                    | Tin (Sn)                    |
| Contact Mating Area Plating Material Finish             | Bright                      |
| Contact Type                                            | Pin                         |
| Contact Current Rating (Max)                            | 4 A                         |
| PCB Contact Termination Area Plating Material           | Tin                         |

Termination Features

|                                  |                |
|----------------------------------|----------------|
| Termination Post & Tail Diameter | .6 mm[.024 in] |
| Termination Method to PCB        | Surface Mount  |

Mechanical Attachment

|                          |              |
|--------------------------|--------------|
| Panel Mount Feature      | With         |
| Mating Alignment Type    | Polarization |
| PCB Mount Retention Type | Solder Peg   |
| PCB Mount Alignment      | Without      |
| Mating Retention         | Without      |
| PCB Mount Retention      | With         |
| Connector Mounting Type  | Board Mount  |
| Mating Alignment         | With         |

Housing Features

|                    |               |
|--------------------|---------------|
| Centerline (Pitch) | 2 mm[.078 in] |
| Housing Material   | 6T PA GF      |

Dimensions

|                             |                       |
|-----------------------------|-----------------------|
| Connector Width             | 5.8 mm[.228 in]       |
| PCB Thickness (Recommended) | .8 mm[.031 – .063 in] |
|                             |                       |



|                  |                 |
|------------------|-----------------|
| Connector Height | 7.8 mm[.307 in] |
| Connector Length | 19.8 mm[.78 in] |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                          |                      |
|--------------------------|----------------------|
| Assembly Process Feature | Pick and Place Cover |
| Circuit Application      | Power & Signal       |

Industry Standards

|                                             |                       |
|---------------------------------------------|-----------------------|
| Compatible With Agency/Standards Products   | CSA, UL               |
| Compatible With Approved Standards Products | CSA LR7189, UL E28476 |
| UL Flammability Rating                      | UL 94V-0              |

Packaging Features

|                    |           |
|--------------------|-----------|
| Packaging Quantity | 700       |
| Packaging Method   | Box, Tape |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                |
| Solder Process Capability                     | Reflow solder capable to 245°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM7017-H8172  
AMP COMMON TERMINATION HOUSINGS

TE Part # 1-353293-3  
MINI CT MT REC ASSY 13P GRAY

TE Part # CAT-AM7017-C7671  
Common Termination Contacts — POWER TRIPLE LOCK

Also in the Series | AMP CT

Connector Contacts(8)

Connector Hardware(39)

PCB Headers & Receptacles(739)

Rectangular Connector Housings(74)

Rectangular Power Connectors(883)

Standard Rectangular Connectors(228)

Wire-to-Board Connector Assemblies & Housings(165)

Wire-to-Board Headers & Receptacles (739)


Customers Also Bought

TE Part #292173-5  
CT BOX HDR H SMT 5P O/TAPE BLA

TE Part #292175-6  
CT BOX HDR V SMT 6P O/TAPE NAT

TE Part #292231-5  
1.5 MINI CT SGL V SMT W/O BOSS

TE Part #292231-6  
1.5 MINI CT SGL V SMT W/O BOSS



Documents

Product Drawings

CT BOX HDR V SMT 9P O/TAPE NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_292175-9\_A1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_292175-9\_A1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_292175-9\_A1.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

Japanese

Product Specification

Japanese