




TE Internal #: 2365211-1
9 Coaxial Contacts, Vertical, Aluminum Alloy, Cable-to-Cable, 9
Position, Wire & Cable, Board Mount, -65 – 120 °C [-85 – 248 °F],
PCB RF Modules
[View on TE.com >](#)

Connectors > RF Connectors > RF Modules > PCB RF Modules



Number of Coaxial Contacts: 9
PCB Mount Orientation: **Vertical**
Body Material: **Aluminum Alloy**
Connector System: **Cable-to-Cable**
Number of Positions: 9

Features

Product Type Features

Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Coaxial Contacts	9
PCB Mount Orientation	Vertical
Number of Positions	9

Body Features

Body Material	Aluminum Alloy
---------------	----------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Usage Conditions

Operating Temperature Range	-65 – 120 °C[-85 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2490866-2
RF .086 Assembly, SMPM Jack - SMA Plug



TE Part # 2332834-2
VITA 67.3 DC MODULE 9 POSITION SS



TE Part # 2490865-2
RF .047 Assembly, SMPM Jack - SMA Plug



TE Part # 2490865-1
RF .047 Assembly, SMPM Jack - SMA Plug



TE Part # 2490867-1
RF .086 Assembly, SMPM Jack - 2.9 Plug



TE Part # 2490872-1
RF .086 Assembly, SMPM Jack - SMPM Jack



TE Part # 2490867-2
RF .086 Assembly, SMPM Jack - 2.9 Plug



TE Part # 2490872-2
RF .086 Assembly, SMPM Jack - SMPM Jack



TE Part # 2332834-3
VITA 67.3 DC MODULE 9 POSITION AL



TE Part # 2332834-1
VITA 67.3 DC MODULE 9 POSITION SS



TE Part # 2332676-1
SMPM CABLE JACK VITA 67-3 SNAP .086



TE Part # 2490866-1
RF .086 Assembly, SMPM Jack - SMA Plug



TE Part # 2490864-2
RF .047 Assembly, SMPM Jack - SMPM Jack



TE Part # 2490864-1
RF .047 Assembly, SMPM Jack - SMPM Jack



TE Part # 2332676-2
SMPM CABLE JACK VITA 67-3 SNAP 047

Customers Also Bought



TE Part #2332834-1
VITA 67.3 DC MODULE 9 POSITION SS

Documents

Product Drawings
MOD 9 POS SMPM VITA 67-3 TYPE A BP
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2365211-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2365211-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2365211-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English