




Connectors > Contacts > Connector Contacts



Contact Type: **Receptacle**

Termination Method to Wire & Cable: **Crimp**

Product Terminates To: **Wire & Cable**

Contact Current Rating (Max): **3 A**

Circuit Application: **Signal**

Features

Contact Features

Contact Type	Receptacle
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025 (250)
Candidate List Declared Against: JUNE 2025 (250)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 4-2393116-1
New GI2.5 HDR ASSY,4P,key A,NTL

TE Part # 3-2393116-2
New GI2.5 HDR ASSY,3P,key B, BLUE


TE Part # 5-2393792-1
New GI2.5 HDR,selected pin,3P,KEY A NTL

TE Part # 3-2393792-1
New GI2.5 HDR,selected pin,2P,KEYA NTL

TE Part # 6-2393116-3
New GI2.5 HDR ASSY,6P,key C, RED

TE Part # 6-2393116-1
NEW GI CONN2.5 HDR ASMBLY 6P NC D1.0

Customers Also Bought



Documents

Product Drawings

NEW GI CONN2.5 REC. CONTACT

English

CAD Files

Customer View Model

ENG_CVM_CVM_2374826-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2374826-1_1.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2374826-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773883-5 GRACE INERTIA connector quick reference guide

English

Product Specifications

Application Specification

English