




TE Internal #: 2386733-1
QSFP112, Cage Assembly, Operating Temperature Range -55 – 85 °C [-67 – 185 °F], Data Rate (Max) 112 Gb/s, 5 Ports, Port Matrix Configuration 1 x 4
[View on TE.com >](#)

Connectors > High Speed Pluggable IO Connectors & Cages



Pluggable I/O Product Type: **Cage Assembly**
Sealable: **No**
Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**
Data Rate (Max): **112 Gb/s**
Number of Ports: **5**

Features

Product Type Features

Cage Type	Ganged
Pluggable I/O Product Type	Cage Assembly
Sealable	No
Form Factor	QSFP112

Configuration Features

Number of Rear EONs per Port Column	2
Number of Ports	5
Port Matrix Configuration	1 x 4

Electrical Characteristics

Data Rate (Max)	112 Gb/s
-----------------	----------

Contact Features

Contact Mating Area Plating Material	Nickel (Ni)
--------------------------------------	-------------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Housing Features

Cage Material	Stainless Steel
---------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Heat Sink Compatible	No
----------------------	----

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2487344-5 QSFP 112G, 26AWG DSD 2.5M	 TE Part # 2487341-2 QSFP 112G, 32AWG DSD 1.0M	 TE Part # 2487344-2 QSFP 112G, 26AWG DSD 1.0M	 TE Part # 2487343-2 QSFP 112G, 28AWG DSD 1.0M
 TE Part # 1-2487344-4 QSFP 112G, 26AWG DSD 5.0M	 TE Part # 2487342-7 QSFP 112G, 30AWG DSD 1.4M	 TE Part # 2487342-8 QSFP 112G, 30AWG DSD 1.8M	 TE Part # 2487344-6 QSFP 112G, 26AWG DSD 1.2M
 TE Part # 2372928-1 QSFP112 Receptacle Assembly, Au	 TE Part # 1-2487344-2 QSFP 112G, 26AWG DSD 0.8M	 TE Part # 2487343-7 QSFP 112G, 28AWG DSD 0.8M	 TE Part # 2487342-2 QSFP 112G, 30AWG DSD 1.0M
 TE Part # 2487341-1 QSFP 112G, 32AWG DSD 0.5M	 TE Part # 2487342-1 QSFP 112G, 30AWG DSD 0.5M	 TE Part # 2487344-1 QSFP 112G, 26AWG DSD 0.5M	 TE Part # 2487344-7 QSFP 112G, 26AWG DSD 1.4M
 TE Part # 2487343-6 QSFP 112G, 28AWG DSD 1.4M	 TE Part # 2487343-1 QSFP 112G, 28AWG DSD 0.5M	 TE Part # 2487342-4 QSFP 112G, 30AWG DSD 1.2M	 TE Part # 2487344-3 QSFP 112G, 26AWG DSD 1.5M

Documents



Product Drawings

CAGE ASSEMBLY, QSFP112 1X5, SPRING

English

Product Specifications

Application Specification

English