




MAG-MATE

TE Internal #: 2-964339-7

Leaf Magnet Wire Terminal, 26 – 23 AWG, .4 – .63 mm, Insulation Displacement (IDC), 3.4 mm [.134 in] Tab Width, Tin Plating, MAG-MATE

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Leaf**
Mating Tab Width: **3.4 mm [.134 in]**
Mating Tab Thickness: **.5 mm [.02 in]**
Compatible With Cavity Size: **Size 2**
Magnet Wire Size: **26 – 23 AWG**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Body Features

Compatible With Cavity Size	Size 2
-----------------------------	--------

Contact Features

Magnet Wire Terminal Type	Leaf
Mating Tab Width	3.4 mm[.134 in]
Mating Tab Thickness	.5 mm[.02 in]
Terminal Plating Material	Tin
Terminal Orientation	Twisted

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Dimensions

Terminal Height	7.9 mm[.311 in]
-----------------	-----------------



Magnet Wire Size	.4 – .63 mm
Stock Thickness (Magnet Wire Side)	.25 mm[.01 in]
Product Length	7.9 mm[.311 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel/Carton
------------------	-------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1740149-3
MAG MATE LEAF TERMINAL MKII



TE Part # 6-1579008-0
INSERTION TOOL



TE Part # 1394759-1
MAG MATE CONT.MKII

Also in the Series | **MAG-MATE**



Insertion & Extraction Tools(3)



Magnet Wire Terminals(327)



PCB Terminals(1)

Customers Also Bought




TE Part #CAT-SIGH262
Signal Header




TE Part #1743486-3
MTII INJECTOR 2P PLUG ASSY



TE Part #936207-4
090III 12P CAP ASSY BROWN




TE Part #2005512-1
SQUIB AK2 CPA



TE Part #2005939-3
SOCKET FOR SQUIB 2P AK-2



TE Part #2109120-2
BULB T20 EXTENSION COVER HSG



TE Part #85193-2
J+MICRO TIMER 55P PLUG ASSY(L)



TE Part #936399-2
MQS 4P CAP ASSY(V-TYPE) BLACK



TE Part #1274232-2
CONTACT,FEMALE,RG62U



Documents

Product Drawings

MAG MATE CONTACT MK II

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-964339-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-964339-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-964339-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

CAVITY FOR 7.62 STANDARD MAG-MATE INTERCONNECT SYSTEM

English

Instruction Sheet (non U.S.)

English