



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **2 Lever Locking**

Features

Product Type Features

Hood & Base Connector Product Type	Base Housing
------------------------------------	--------------

Body Features

Cable Entry Location	Bottom
----------------------	--------

Mechanical Attachment

Hood & Base Locking Device Type	2 Lever Locking
---------------------------------	-----------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2390402-1
DYNAMIC FRAME CABLE W KEY 2 MODULE

Customers Also Bought



TE Part #5-1473571-8
RITS.JUNCTION BOX 2D 8P F/H



TE Part #2311162-2
DYNAMIC D-3 FMLB REC CONT AU0.38 M L/P



TE Part #2316669-1
HD1 TAB CONTACT AU0.38 S SIZE L/P



TE Part #2390402-1
DYNAMIC FRAME CABLE W KEY 2 MODULE





TE Part #2316671-1
HD1 REC CONTACT AU0.38 S SIZE L/P



TE Part #3-1473562-8
RITS CONN. PLUG ASSY 8P ORANGE

TE Part #2260110-2
MINI IO PIERCING CABLE ASSY L2000

TE Part #2260110-7
MINI IO PIERCING CABLE ASSY L1500



Documents

Product Drawings

[DYNAMIC FRAME PANEL W KEY 2 MODULE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2390404-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2390404-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2390404-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[DYNAMIC CONNECTOR SERIES ACCESSORY PARTS](#)

Japanese

[Product Specification](#)

Japanese