




Cable Assemblies > Copper Cable Assemblies > Internal I/O Cable Assemblies



Cable Assembly Type: AMP CT to AMP CT

Cable Style: Discrete Pair

Number of Positions: 4

Number of Signal Positions: 4

Wire Size: 28 AWG

Features

Product Type Features

Cable Assembly Type	AMP CT to AMP CT
Cable Style	Discrete Pair

Configuration Features

Number of Positions	4
Number of Signal Positions	4

Dimensions

Wire Size	28 AWG
-----------	--------

Other

Cable Assembly Length	.3 m[.98 ft]
-----------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 292215-4 MINI CT SGL RELAY 4P NAT	 TE Part # 292228-4 1.5 MINI CT SGL H SMT W/O BOSS	 TE Part # 292230-4 1.5 MINI CT SGL V SMT W/BOSS 4	 TE Part # 292227-4 1.5 MINI CT SGL H SMT W BOSS 4
 TE Part # 292207-4 MINI CT SGL DIP V 4P NAT	 TE Part # 2106091-3 4 pos Inverted Thru Board SMT Header	 TE Part # 292206-4 MINI CT SGL DIP H 4P NAT	

Customers Also Bought





TE Part #ANT-868-CW-RCL-SMA
Antenna 1/2 Wave R-Angle 868MHz
SMA




TE Part #MS580502BA01-50
MINIATURE DIGITAL PRESSURE
SENSOR




TE Part #20009605-14
FX293X-100A-0050-L



TE Part #T41613B9L25-002
RPC-M12L-5FS-1.0-SH PUR 14AWG GY




TE Part #282834-6
TERMI-BLOK PCB MOUNT, 90 6P.



TE Part #282836-4
TERMI-BLOK PCB MOUNT 90 4P.




TE Part #1571527-2
FSM2JSMLTR=TACT SWITCH,SMT,
T&R



TE Part #2405870-3
CT 3P 300MM CABLE ASSEMBLY 6-
353908-3



TE Part #5050864-1
SOCKET,MIN-SPR SN-AU SER-3



TE Part #3198143001
ACW0219-2.50-9(NS)

Documents

Product Drawings

CT 4P 300MM CABLE ASSEMBLY 6-353908-4

English

CAD Files

Customer View Model

ENG_CVM_CVM_2405870-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2405870-4_A.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2405870-4_A.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



6-1773454-5_AMP_Mini_CT_Connector_Series_QRG

English