

SMQW33R0JT

✓ ACTIVE

CGS | CGS SMQ


TE Internal #: 3-2176617-6

3 ohm, Wire Wound, Power Resistor, 5 %, 3 W, ±200 ppm/°C,
Solder, 2 Terminations, 6.8 mm [.268 in] Height, 13.5 mm [.531 in]
Length, CGS SMQ

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**
Element Type: **Wire Wound**
Power Rating: **3 W**
Resistance Value: **3 Ω**
Resistance Class: **Up to 1kΩ**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Power Rating	3 W
Resistance Value	3 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2



Dimensions

Product Height	6.8 mm[.268 in]
Product Length	13.5 mm[.531 in]
Product Width	7.3 mm[.287 in]

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
Temperature Coefficient	±200 ppm/°C

Industry Standards

UL Flammability Rating	UL 94V-0
Industry Standard	AEC-Q200 Compliant
ESD HBM Classification	2
Moisture Sensitivity Level	1

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

SMQW33R0JT

3 ohm, Wire Wound, Power Resistor, 5 %, 3 W, ±200 ppm/°C, Solder, 2 Terminations,
6.8 mm [.268 in] Height, 13.5 mm [.531 in] Length, CGS SMQ



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 3-2176617-7
SMQW3W 3R3 5%

TE Part # 3-2176617-5
SMQW3W 2R7 5%

Also in the Series | CGS SMQ

[Surface Mount Resistors\(528\)](#)

Customers Also Bought

TE Part #NB13542001
RNF-100-3/8-BK-STK

TE Part #1-1614884-4
CPF 0805 7R5 0.1% 25PPM 1K RL

TE Part #1623536-1
CRG1206 1% 56K

TE Part #1623550-1
CRG1206 1% 68K

SMQW33R0JT

3 ohm, Wire Wound, Power Resistor, 5 %, 3 W, ±200 ppm/°C, Solder, 2 Terminations,
6.8 mm [.268 in] Height, 13.5 mm [.531 in] Length, CGS SMO



TE Part #4-1879233-0
[SMW5 4R3 5%](#)

TE Part #9-1879514-4
[CRGH1206 1% 1K0 0.5W](#)

TE Part #6-2176230-4
[3522 150K 5% 3W](#)

TE Part #3-2176617-2
[SMQW3W 2R0 5%](#)

TE Part #4-2176617-5
[SMQW3W 6R8 5%](#)

TE Part #4-2176617-7
[SMQW3W 8R2 5%](#)

Documents

Product Drawings

[SMQW3W 3R0 5%](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-2176617-6_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2176617-6_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2176617-6_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD_MOULDED_POWER_RESISTOR](#)

English