HSC150S33RJ ✔ ACTIVE




CGS | CGS HS

TE Internal #: 3-2176732-1

33 ohm, Wire Wound, 5 %, Power Resistor, 150 W, 2 Terminations, ±50 ppm/°C, Screw Terminals, Loose Piece - Tray, 23 mm [.906 in] Height, CGS HS

View on TE.com >

Passive Components > Resistors > Chassis Mount Resistors > Power Resistors: Aluminium Housed, HSC



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1kΩ**

Resistance Value: **33 Ω**

Power Rating: **150 W**

Element Type: **Wire Wound**

All Power Resistors: Aluminium Housed, HSC (485)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	2500 VDC
Resistance Class	Up to 1kΩ
Resistance Value	33 Ω
Power Rating	150 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2

Chassis Mount Resistor Termination Type	Screw Terminals

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes

Dimensions

Product Height	23 mm[.906 in]
Product Length	125.6 mm[4.945 in]
Product Width	47 mm[1.85 in]

Usage Conditions

Temperature Coefficient	±50 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the

product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-C339-H85913B
Power Resistors: Aluminium Housed, HSC


Also in the Series | CGS HS




Automotive Housings(1)




Automotive Signal & Power Connector Housings(1)



Card Edge Connector Housings(1)



FFC Connectors(1)




High Speed Backplane Connectors(10)




RJ45 Connectors(1)

Customers Also Bought




TE Part #521393-000
301A011-25/225-0



TE Part #F94898-000
S200-2-00



TE Part #YD369-P66-NP300000
369 6 WAY PLUG, 20/22 CONTACTS, PIN



TE Part #F92583-000
S200-1-00



TE Part #2-34111-3
SOLIS R 22-16 COMM 22-18 MIL 8



TE Part #1-51864-1
TERMINAL,PIDG R IR 14 8



TE Part #7-1614894-7
CPF0805 2M0 0.1% 25PPM 5K RL



TE Part #2-1630012-9
HSC150 47R 5%

TE Part #39364
DAHT HOLD DOWN SPRING

TE Part #6-1768383-4
LBF-2000P-RIBBON-1966-MED

Documents

Product Drawings

HSC150S 33R 5% Screw Terminal

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-2176732-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2176732-1_A.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2176732-1_A.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Aluminium Housed Power Resistors - Type HS Series

English