



AMP

TE Internal #: 2822355-1

Rubber Plug, 1.8 mm [.07 in] Cavity Diameter, -30 – 105 °C [-22 – 221 °F], Black, NBR, 1.8 – 2.6 mm [.071 – .102 in] Insulation Diameter

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Rubber Plug**

Cavity Diameter: **1.8 mm [.07 in]**

Operating Temperature Range: **-30 – 105 °C [-22 – 221 °F]**

Primary Product Color: **Black**

Primary Product Material: **NBR**

**Features**

**Product Type Features**

Connector Seal & Plug Type	Rubber Plug
----------------------------	-------------

**Body Features**

Primary Product Color	Black
Primary Product Material	NBR

**Dimensions**

Cavity Diameter	1.8 mm[.07 in]
Compatible Insulation Diameter Range	1.8 – 2.6 mm[.071 – .102 in]

**Usage Conditions**

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
Operating Temperature (Max)	105 °C[212 °F]

**Industry Standards**

UL Flammability Rating	UL 94V-2
------------------------	----------

**Packaging Features**

Packaging Method	Bag
------------------	-----



Packaging Quantity	1000
--------------------	------

### Other

Resistance to Hydrocarbons	Poor
----------------------------	------

Shore A Hardness	40
------------------	----

Contains Lubricant	Yes
--------------------	-----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Out of Scope
-----------------------------	--------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



### Customers Also Bought



### Documents

#### Product Drawings

070 TYPE RUBBER PLUG M

Japanese

#### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2822355-1\_A.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2822355-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2822355-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications

[Product Specification](#)

Japanese

[Product Specification](#)

English

[Product Specification](#)

Japanese