


THIS DRAWING IS A CONTROLLED DOCUMENT.


DWG NO
354578

PART NUMBER	REV	FIRST USED
354578-1	F	354500-1
354578-2	G	-

USED ON G-TERM




354578-1



354578-2

1. RECOMMENDED SPARE PARTS - NONE.
2. APPLY ITEM 6 TO ALL FITTINGS AS REQUIRED.
3. NOT SHOWN. SHIPPED LOOSE.
4. REMOVE BURRS, BREAK SHARP EDGES R.015 MAX UNLESS OTHERWISE SPECIFIED.



SCREWS TO MOUNT VALVE BRACKET

VALVE CONNECTION

CPC CONNECTOR

INSTALLATION INSTRUCTIONS:

1. LOCATE THE 2 POSITION CONNECTOR THAT COMES OUT OF THE INDICATED CPC CONNECTOR LOCATED NEAR THE FRONT OF PRESS.
2. ATTACH THE CONNECTOR TO THE VALVE.
3. ATTACH THE VALVE BRACKET TO THE PRESS USING 2 SCREWS.

1	-	-	980282-3	CONN,TUBE,MALE	12
1	-	-	22311-1	1/8 NPT NIPPLE	11
1	-	-	18273-1	VALVE,CHECK	10
1	1	-	354578	PRINT,AIR FEED ASSY	9
1	1	-	354579-1	VALVE ASSEMBLY	8
2	2	-	986941-4	SCR,LOCKING,SOCKET,M6 x 12mm	7
AR	AR	-	1-23419-1	SEALANT, LOCTITE	6
-	1	-	354589-1	FILTER ASSEMBLY	5
-	-	-	-	-	4
-	-	-	-	-	3
-	-	-	-	-	2
1	1	-	354585-1	BRACKET, VALVE	1
-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

QTY REQD PER ASSY			PARTS LIST		
			DWN	28MAY99	MATERIAL
			CHK	-	HEAT TREAT
			APVD	28MAY99	
			NAME	AIR FEED ASSEMBLY	
			SCALE	SIZE	DRAWING NO
			-	A1	354578
			SHEET	1	OF 1
			REV	G1	

CUSTOMER ACCESSIBLE PRODUCTION DRAWING

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TFCO. IT IS TO BE KEPT CONFIDENTIAL AND NOT DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TFCO. ANY VIOLATION OF THIS POLICY WILL BE CONSIDERED A BREACH OF EMPLOYMENT AND WILL BE CAUSE FOR IMMEDIATE DISCIPLINE, UP TO AND INCLUDING TERMINATION.

LOC
A
DIST
33

3308-8 (3/11)

8

7

6

5

4

3