



Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 60
Primary Product Color: Black
Protection & Strain Relief Accessory Type: Cover Assembly
Primary Product Material: PA GF
Strain Relief: With

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover Assembly
---	----------------

Configuration Features

Number of Positions	60
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PA GF

Mechanical Attachment

Strain Relief	With
---------------	------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	500



Other

Serviceable	No
-------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1534903-1
CONNECTOR HSG 60 POS.



TE Part # 1-1579007-2
EXTRACTION TOOL



TE Part # 284723-1
COVER FOR 60 POS RECEPTACLE HO

Also in the Series | AMP MCP Connector System




Automotive Connector Caps & Covers (28)



Automotive Housings(242)



Automotive Signal & Power Headers(5)



Automotive Terminals(7)



Other Automotive Connector Accessories(4)

Customers Also Bought



TE Part #CAT-PA3-RB
EMC/RFI Chokes RB Series: Current-Compensated Chokes for High-Performance Filtering



TE Part #CAT-H3930-CH8172
DEUTSCH HD30 Housings



TE Part #42566-2
187 FASTON REC 20-16 AWG TPBR



TE Part #2098253-1
SOC, SF, SIZE 16, 14-16 AWG, AU/SN




TE Part #9-2141157-1
SHIELD CRIMP FERRULE,90DEG



TE Part #2141262-3
SHIELDING,EMC



TE Part #2292799-3
AS16,PLUG BACKSHELL KIT,ST,04P, NC12



TE Part #828801-2
2X 3P MESSERLEI 3,0

Documents

Product Drawings
ASS'Y COVER 60 POS AND CPA
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_284726-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_284726-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_284726-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English