2-84953-4 ✔ ACTIVE

FPC

TE Internal #: 2-84953-4

1 mm [.039 in] Centerline, Zero Insertion Force (ZIF), Right Angle, Surface Mount, Stuffer Actuator, Tin (Sn), 24 Position, FPC Connectors

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors



Centerline (Pitch): **1 mm [.039 in]**

Insertion Force Type: **Zero Insertion Force (ZIF)**

PCB Mount Orientation: **Right Angle**

Contact Mating Location: **Top**

Termination Method to PCB: **Surface Mount**

Features

Product Type Features

PCB Connector Type	PCB Mount Receptacle
Connector & Contact Terminates To	Flexible Printed Circuit (FPC)
Connector Product Type	Connector Assembly
Connector System	Flex-to-Board
Insertion Force Type	Zero Insertion Force (ZIF)
FPC Actuator Type	Stuffer

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	1
PCB Mount Orientation	Right Angle
Number of Positions	24

Electrical Characteristics

Operating Voltage	200 VAC

Body Features

Primary Product Color	Natural

Contact Features

Contact Current Rating (Max)	1 A
PCB Contact Termination Area Plating Material Thickness	2 µm, 3.8 µm

Contact Shape & Form	Single Beam
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
PCB Contact Termination Area Plating Material Finish	Bright
Contact Type	Socket
Contact Mating Area Plating Material Thickness	2 µm, 3.8 µm
Contact Mating Area Plating Material Finish	Bright
Contact Mating Location	Top
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Surface Mount

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Retention	With
PCB Mount Alignment	Without

Housing Features

Housing Material	Liquid Crystal Polymer (LCP)
Centerline (Pitch)	1 mm[.039 in]

Dimensions

Connector Width	6.54 mm[.258 in]
Accepts Flex Cable Thickness	.3 mm[.012 in]
Connector Height	2.56 mm[.101 in]
Connector Length	31.92 mm[1.257 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Operation/Application

Circuit Application	Signal

Identification Marking

Circuit Identification Feature	With

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	1200

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 2-84982-4
1MM FFC SMT V ASSY 24P EMBOSS



TE Part # 2-84952-4
1MM FPC HORZ.BOTTOM CONT. ASSY 24P


Customers Also Bought



TE Part #154765-E
SMCB 50 M AB VV 7-03 CL * 0007 137 E004



TE Part #1-84953-4
1MM FPC HORZ.TOP CONT.ASSY 14P



TE Part #103638-2
03 MTE HDR SRST LATCH .100CL



TE Part #8-1393222-1
V23061B1003A501=MINISTARKSTROM



TE Part #2227303-2
CAGE ASSEMBLY, SFP, .071 TAIL



TE Part #6609053-9
10EHT1=F7667 S0



TE Part #829111-4
96P MOD2 ST-WANNE

TE Part #7-1768412-5
LBG-U-03152/EET0606

TE Part #3-1768421-7
LBG-U-03194/4/EET0814



TE Part #5917628-2
REC ASS'Y(V) 60P 1.27FHBB

Documents

CAD Files

3D PDF

3D

Customer View Model
ENG_CVM_CVM_2-84953-4_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_2-84953-4_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_2-84953-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1-1773959-7-FPC-Connectors-CN

English

FPC Connector Family

English

Product Specifications

Product Specification

English

Agency Approvals

UL Report

English