



Automotive Parts > Automotive Connectors > Automotive Housings > Timer Connector Housing



Nominal Voltage Architecture: 12 V

Connector & Housing Type: **Housing for Male Terminals**

Number of Positions: 6

Sealable: No

Operating Temperature Range: -40 – 80 °C [-40 – 176 °F]

[All Timer Connector Housing \(436\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Sealable	No
Primary Locking Feature	Locking Lance
Connector System	Wire-to-Panel
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	2

Electrical Characteristics

Nominal Voltage Architecture	12 V
------------------------------	------



Body Features

Primary Product Color	Gray
Connector & Keying Code	B1

Contact Features

Contact Size	2.8mm
Contact Type	Tab
Mating Tab Width	2.8 mm[.11 in]
Contact Current Rating (Max)	30 A

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PBT GF30
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Product Width	38 mm[1.49 in]
Row-to-Row Spacing	6 mm[.236 in]
Product Length	26.6 mm[1.05 in]
Connector Height	22.3 mm[.88 in]

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
Operating Temperature (Max)	80 °C[176 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Carton
Packaging Quantity	1500

Other

Serviceable	No
-------------	----



Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-963212-9
6P J-P-T GEH KOMPL



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 2-1452319-1
JPT HOUSING SEAL 6P



TE Part # CAT-T4827-CH8172
Timer Connector Housing



TE Part # 963205-1
SEAL

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers
(12)




Automotive Housings(186)



Automotive Seals & Cavity Plugs(32)



Automotive Signal & Power Headers(6)



Automotive Terminals(110)



Quick Disconnects(4)

Customers Also Bought



TE Part #HDP26-18-14PE
PLG, 14P, BLK, E, 16, P




TE Part #DRC22-40PA
40P RECP ASM



TE Part #66740-7
TYPE XII FEMALE CONT (STRIP)



TE Part #880310-1
2 WAY FF 250 HOUSING TAB NYLON
6.6 NAT



TE Part #927773-3
JPT REC 2.8 Contact SRC Sn



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #1437284-9
MERTEC FTERM AU 13002630101



TE Part #1717675-1
CAP ASSY,6P,BRACKET REVERSE TY



TE Part #1735447-4
HPI 2.0 RECEPTACLE HOUSING, 4P

Documents

Product Drawings

6P STIFT-GEH 3MM

English

CAD Files

Customer View Model

ENG_CVM_2-962349-1_E1.3d_igs.zip

English

Customer View Model

ENG_CVM_2-962349-1_E1.3d_stp.zip

English

Customer View Model

ENG_CVM_2-962349-1_E1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

889759_3_Timer_Interconnection_System

English