



Connectors > PCB Connectors > Backplane Connectors > Backplane Guide Hardware



Backplane Guide Hardware Type: **Guide Pin Module**

Backplane Guide Location: **Front Board**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Backplane Guide Hardware Type	Guide Pin Module
-------------------------------	------------------

Configuration Features

Backplane Guide Location	Front Board
--------------------------	-------------

Body Features

Guide Component Plating Material	Nickel
Guide Component Base Material	Zinc Alloy

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JUN 2020
(209)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content
Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability
Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1766876-1
PLATED CONTACT,SKT BOD

Customers Also Bought

TE Part #17-015A
BOARD LEVEL PRESSURE STOCK LIST

TE Part #1-1969688-4
POWER TRIPLE LOCK HIGH TEMP HEADER

TE Part #2132415-9
EP2.5 Shrouded HDR ASSY 9P VERT w /o boss

TE Part #1888653-5
2X1 OFFSET ST/JK WITH LEDS



TE Part #1871058-3
PCI EXPRESS CONN. EON TYPE, 98



TE Part #1744426-9
Header Housing Assy, EP 2.5 RA, 9 Pos.



TE Part #2305234-1
SOCKET P HARDWARE DUST COVER



TE Part #1871916-1
SD RVS 0H EMBOSS ASSY



TE Part #1982995-3
CROWN CLIP JUNIOR SCREW-MOUNT CONN



TE Part #6450839-6
MBXLE R/A HDR 2ACP8S4ACP16S2AC

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_3-1410947-8_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1410947-8_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1410947-8_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[TE Material Declaration](#)

English