




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: PCB Mount Header

PCB Mount Orientation: Vertical

Connector System: Wire-to-Board

Number of Positions: 2

Centerline (Pitch): 7.92 mm [.312 in]

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	2
Number of Loaded Positions	2
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1



Number of Power Positions	2
Electrical Characteristics	
Operating Voltage	300 VDC
Body Features	
Connector & Keying Code	D
Primary Product Color	Green
Contact Features	
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.8 – 3 µm[31.496 – 118.11 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Mating Tab Width	1.5 mm[.059 in]
PCB Contact Termination Area Plating Material Thickness	1 µm[39.36 µin]
Contact Shape & Form	Rectangular
Contact Layout	Inline
Contact Mating Area Length	6 mm[.236 in]
Contact Base Material	Copper Alloy
Mating Tab Thickness	.5 mm[.02 in]
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Contact Type	Tab
Contact Current Rating (Max)	10 A
PCB Contact Termination Area Plating Material	Tin
Termination Features	
Rectangular Termination Post & Tail Width	1.1 mm[.043 in]
Rectangular Termination Post & Tail Thickness	.5 mm[.02 in]
Termination Post & Tail Length	3.7 mm[.146 in]
Termination Method to PCB	Through Hole - Solder
Mechanical Attachment	
Panel Mount Feature	Without
Mating Retention Type	Locking Window
Mating Alignment Type	Keyed



PCB Mount Retention Type	Kinked Legs
PCB Mount Alignment Type	Locating Posts
PCB Mount Alignment	With
Mating Retention	With
PCB Mount Retention	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Mating Entry Location	Top
Centerline (Pitch)	7.92 mm[.312 in]
Housing Material	Nylon 6/6 GF

Dimensions

Connector Width	11.75 mm[.462 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	14.5 mm[.57 in]
Connector Length	14.97 mm[.589 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	250
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant







China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1747052-5 GIC7.92 2POS_HDR ASS'Y GREEN KEYING B	 TE Part # 1747052-3 GIC7.92 2POS_HEADER ASSY BLUE KEYING B	 TE Part # 2-1747052-5 GIC7.92 2POS_HDR ASS'Y GREEN KEYING C	 TE Part # 1-1747052-2 GIC 7.92MM CONN HDR ASS'Y 2POS RED
 TE Part # 1-1747052-3 GIC7.92 2POS_HEADER ASS'Y BLUE KEYING B	 TE Part # 1-1747052-1 GIC7.92 2POS_HEADER ASS'Y NAT KEYING B	 TE Part # 1747052-4 GIC7.92 2POS_HEADER ASS'Y YELLO KEYING A	 TE Part # 1747052-5 GRACE INERTIA CONNECTOR 7.92 2POS HEADER



TE Part # 1747052-2
GIC7.92 2POS_HEADER ASS'Y RED
KEYING A

TE Part # 1747052-1
GRACE INERTIA CONNECTOR 7.92
2POS_HEADER

Also in the Series | GRACE INERTIA 7.92

PCB Headers & Receptacles(21)

Rectangular Connector Housings(18)

Rectangular Power Connectors(39)

Standard Rectangular Connectors(18)

Wire-to-Board Connector Assemblies
& Housings(18)

Wire-to-Board Headers & Receptacles
(21)

Customers Also Bought

TE Part #1-1747052-1
GIC7.92 2POS_HEADER ASS'Y NAT
KEYING B

TE Part #1-1747052-4
GIC7.92 2POS_HDR ASS'Y YELLOW
KEYING B

TE Part #2-1747052-2
GIC7.92 2POS_HDR ASS'Y RED
KEYING C

TE Part #2-1747052-5
GIC7.92 2POS_HDR ASS'Y GREEN
KEYING C

TE Part #3-1747052-3
GIC7.92 2POS_HDR ASS'Y BLUE
KEYING D

TE Part #1871843-5
GIC2.5 HDR ASSY TIN VERSION 5P
NATURAL

TE Part #1871843-8
GIC2.5 HDR ASSY TIN VERSION 8P
NATURAL

TE Part #1-1871843-6
GIC2.5 HDR ASSY TIN VERSION 6P
RED



Documents

Product Drawings

GIC7.92 2POS_HDR ASS'Y GREEN KEYING D

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-1747052-5_F.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1747052-5_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1747052-5_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English