





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASE TO PRODUCTION	25MAY2020	RK	JO



- 1 0.000381 [.000015] GOLD IN THE CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 THE NOTED DIMENSIONS APPLY FROM THE BASIC DIMENSION LINE (NOT THE POST CENTERLINE) TO THE SURFACE INDICATED
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 DIMENSIONS NOTED ARE FOR SOLDER STENCIL LAYOUT FOR USE WITH A 1.57±0.20 [.062±.008] THICK. PRINTED CIRCUIT BOARD
- 6 PARTS ARE PACKAGED IN GANG OF TUBES
- 7 0.000381 [.000015] GOLD IN THE CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON THE SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.

SECTION X-X

RECOMMENDED PC BOARD MOUNTING DIMENSIONS
RECOMMENDED STENCIL THICKNESS = 0.25 [.010]

7	20.19 [.795]	18.29 [.720]	15.24 [.600]	6	7	5-2267760-7
PLATING	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25MAY2020 RAGHAVENDRA.K				
DIMENSIONS: mm		CHK 25MAY2020 J.OLSON				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 25MAY2020 J.OLSON	NAME			
0 PLC ± -		PRODUCT SPEC	HDR ASSY, AMPMODU MTE, RT ANG			
1 PLC ± -		APPLICATION SPEC	SINGLE ROW, .100 POSTS W/ LATCH, HD			
2 PLC ± 0.13 [.005]			.200 LEADS			
3 PLC ± -			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± -			A2	00779	C=2267760	-
ANGLES ± -			SCALE 4:1 SHEET 1 OF 1 REV A			
FINISH SEE TABLE		WEIGHT -	CUSTOMER DRAWING			