

DPL12SVN24A21F3

✓ ACTIVE

Citec | Citec DP

TE Internal #: 3-1879314-5

24 Pulse, Red/Green LED, LED Encoder, None Detent, 14.5 x 12.4 x 7 mm, Top Adjustment, Push Push SPDT, .01 A Switch Current, Vertical, Citec DP

[View on TE.com >](#)



Passive Components > Resistors > Rotary Encoders



Number of Pulses: **24**

Encoder Type: **LED Encoder**

Shaft Style: **Flatted**

Number of Detents: **None**

Passive Component Dimensions: **14.5 x 12.4 x 7 mm**

Features

Product Type Features

Passive Component Option	Includes Switch
Encoder Type	LED Encoder
Rotary Encoder Switch Type	Push Push SPDT

Configuration Features

Adjustment Method	Spindle
Number of Pulses	24
Number of Detents	None
Adjustment Location	Top

Electrical Characteristics

Passive Component Switch Current Rating	.01 A
---	-------

Body Features

Shaft Style	Flatted
LED Color	Red/Green
Product Orientation	Vertical

Termination Features

Product Terminates To	Printed Circuit Board
-----------------------	-----------------------

Dimensions

Passive Component Dimensions	14.5 x 12.4 x 7 mm
------------------------------	--------------------



Operation/Application

Operating Speed (Max)	60 RPM
-----------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1879314-1 DPL12 24P NDET 20F BLUE	 TE Part # 1-1879749-7 LED ENCODER 12MM HORIZ SW GR /RD	 TE Part # 2-1879749-3 LED ENCODER 12MM HORIZ SW GR /RD	 TE Part # 4-1879314-7 DPL12S 24P 24DET 21F RD/GRN /RD
--	--	---	--

DPL12SVN24A21F3

24 Pulse, Red/Green LED, LED Encoder, None Detent, 14.5 x 12.4 x 7 mm, Top Adjustment, Push Push SPDT, .01 A Switch Current, Vertical, Citec DP



TE Part # 4-1879314-5
DPL12S 24P 24DET 25K RD/GRN

Also in the Series | Citec DP



Rotary Encoders(856)

Customers Also Bought



TE Part #ANT-868-CHP-T
Antenna Chip T&R 868MHz SMT



TE Part #7-1393239-8
RT314A05



TE Part #8-1393239-5
RT314F05



TE Part #5-1879021-9
SMW3 27R 5%



TE Part #6-1879021-1
SMW3 33R 5%



TE Part #2173157-3
MICRO USB, TYPE B, SPLASHPROOF (LOW MOQ)

Documents

Product Drawings

DPL12S 24P NDET 21F RD/GRN

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-1879314-5_BB.3d_igs.zip

DPL12SVN24A21F3

24 Pulse, Red/Green LED, LED Encoder, None Detent, 14.5 x 12.4 x 7 mm, Top Adjustment, Push Push SPDT, .01 A Switch Current, Vertical, Citec DP



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1879314-5_BB.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1879314-5_BB.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[1-1773449-0](#)

English