

SMQW11R8JT

✓ ACTIVE

CGS | CGS SMQ

TE Internal #: 3-2176615-1

1.8 ohm, Wire Wound, Power Resistor, 5 %, 1 W, ±200 ppm/°C,
Solder, 2 Terminations, 3.55 mm [.14 in] Height, 6.7 mm [.264 in]
Length, CGS SMQ

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**
Element Type: **Wire Wound**
Power Rating: **1 W**
Resistance Value: **1.8 Ω**
Resistance Class: **Up to 1kΩ**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	300 V
Power Rating	1 W
Resistance Value	1.8 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2



Dimensions

Product Height	3.55 mm[.14 in]
Product Length	6.7 mm[.264 in]
Product Width	4 mm[.157 in]

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
Temperature Coefficient	±200 ppm/°C

Industry Standards

UL Flammability Rating	UL 94V-0
Industry Standard	AEC-Q200 Compliant
ESD HBM Classification	2
Moisture Sensitivity Level	1

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

SMQW11R8JT

1.8 ohm, Wire Wound, Power Resistor, 5 %, 1 W, ±200 ppm/°C, Solder, 2 Terminations, 3.55 mm [.14 in] Height, 6.7 mm [.264 in] Length, CGS SMQ



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 3-2176615-0
SMQW1W 1R6 5%

TE Part # 3-2176615-2
SMQW1W 2R0 5%

Also in the Series | CGS SMQ

Surface Mount Resistors(528)


Customers Also Bought

TE Part #254154-E
M8 METAL SHELL, FEMALE, VERT, 9MM

TE Part #CSI-SGFE-200-UFFR
SMA to U.FL/MHF1 200mm 1.13 OD

TE Part #T4041037041-000
M8.FMLE.PNLREAR.4POS.STR PCBSHLD


TE Part #1622555-1
LR1 1% 6K8




TE Part #1-1705949-1
Modular Jack SE, 4/4, Gold flash



TE Part #9-1879225-0
CPF 0603 383K 0.1% 25PPM 1K RL




TE Part #7-1879417-9
CPF0603 806K 0.1% 25PPM 1K RL



TE Part #1-2176280-4
CPF 0402 140K 0.1% 25PPM 1K RL



TE Part #2199119-1
M.2 0.5PITCH 3.2H KEY B GOLDFLASH



TE Part #2311763-3
AMPL REC, HD22, R/A, 15P, THREADED

Documents

Product Drawings

SMQW1W 1R8 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2176615-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2176615-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2176615-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD_MOULDED_POWER_RESISTOR

English