




COIL: 26.5 VDC @ 25°C

WINDING #1

1000 OHMS ± 10% @ 25° C

13.0 VDC MUST OPERATE

26.5 VDC NOMINAL VOLTAGE

WINDING #2

1000 OHMS ± 10% @ 25° C

13.0 VDC MUST OPERATE

26.5 VDC NOMINAL VOLTAGE

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 30 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C


NOTES: OTHER SPECIFICATIONS IN ACCORDANCE
WITH MIL-R-39016/45

OPERATE TIME 5 MS MAX.

BOUNCE 2.0 MS MAX.

CUSTOMER DATA SHEET

LAST ENERG.



CONTACT RATING: LOW LEVEL TO 2 AMPS
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 5/17/96 CK. 5/17/96

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. COMMERCIAL REF.
CUST. NO. M39016/45-023L

TYPE "LS" RELAY

LS-9523L