




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 509 – 3260 CMA

Stud Size: M5

Features

Product Type Features

Terminal Features	Sheared
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Product Weight	.628 g
Insulation Sleeve Color	Red
Stripe Color	Red

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight



Terminal Plating Material	Tin
---------------------------	-----

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	5.7 mm [.224 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	21.87 mm [.86 in]
Compatible Insulation Diameter (Max)	3.56 mm [.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm [.105 – .14 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	0 – 90 °C [0 – 194 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 59300 T-HEAD PIDG PG 26-16 ASSY	TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	TE Part # 47806-2 DIES PIDG 22-16 DIE SET	TE Part # 47386 DAHT PG PIDG 26-16 ASSY
TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 59170 T-HEAD PIDG SH 26-14 ASSY	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 59250 T-HEAD PIDG 26-14 ASSY
TE Part # 2063030-1 SDE DIESET, RBY, UL	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 169404 CERTI-LOK DIE	

Also in the Series | **PLASTI-GRIP**




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)



Spade Terminals(158)



Splices(45)


Customers Also Bought



TE Part #2-32951-1
PG R 22-16 COMM 22-18 MIL 8




TE Part #58508-1
PRO-CRIMPER HD TL W/DIE BUDGET



TE Part #345809-1
.070" TAB ECONOSEAL 3



TE Part #3-1630024-7
HSC250 200R 5%




TE Part #6-2176388-1
RQ 1206 42R2 0.1% 10PPM 5K RL



TE Part #2176444-3
HCF166 160W 33R 5% LEAD



TE Part #1-2213766-5
AV19 SPM 3A POWER LED GREEN 24V



TE Part #M3431-000006-01KPG
PRESS XDCR M3431-000006-01KPG



TE Part #1-1587987-7
RECEPTACLE ASSEMBLY, Shunt, MSD



TE Part #1-2103172-7
Plug Assembly, Shunt, MSD

Documents



Product Drawings

22-16 F.E.P.G.RING TONGUE'0BA'

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_342104-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_342104-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_342104-1_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PLASTI GRIP_QRG

English

Product Specifications

Application Specification

English