



TE Internal #: 603502-3
Red, Butt Splice, 22 – 18 AWG, .3 – .9 mm² Wire, 509 – 1900 CMA,
Fully Insulated, Sealable, Copper, 43 mm [1.693 in] Length, Loose
Piece
[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Butt Splice**
Wire Size: **.3 – .9 mm²**
Sealable: **Yes**
Compatible Insulation Diameter Range: **4 mm [.17 in]**

Features

Product Type Features

Splice Type	Butt Splice
Sealable	Yes
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

	.003 oz
Insulation Material	Nylon
Insulation Type	Pre-Insulated
Primary Product Color	Red

Contact Features

Terminal Plating Material	Tin
---------------------------	-----



Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Recovered Inside Diameter	1.65 mm[.065 in]
Outside Diameter	4.45 mm[.175 in]
Wire Size	509 – 1900 CMA
Compatible Insulation Diameter Range	4 mm[.17 in]
Barrel Inside Diameter	4 mm[.17 in]
Product Length	43 mm[1.693 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #66102-6 III+ PIN, 24-20, 30AU >10, STRIP	TE Part #103455-1 MOD V RECP PLTD 30 AU	TE Part #1-104257-7 18 MTE RCPT HSG SR LATCH .100	TE Part #640915-2 RECEPT, PIDG FASTON 16-14 205
TE Part #640923-2 RECEPT, PIDG, FASTON, .110 SERIES, 22-18	TE Part #640929-2 RECEPT, PIDG FASTON 16-14 110	TE Part #794193-1 08P MINI UMNL2 CAP HSG UL94V0	TE Part #794230-1 MINI UMNL2 PIN 20-16AWG LP SN
TE Part #926298-7 UNIVERSAL MATE-N-LOK 4 WAY PLUG	TE Part #7-6437144-0 FSN-23A-6		

Documents

Product Drawings
PRE-INSUL SEALED SPLICE 22-16

English

CAD Files
3D PDF



3D

Customer View Model

[ENG_CVM_CVM_603502-3_K.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_603502-3_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_603502-3_K.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_603502-3_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_603502-3_N.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_603502-3_N.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.