6-1355134-1 ✔ ACTIVE

MQS


TE Internal #: 6-1355134-1

94 Position, Violet, Retainer, PBT GF30, -40 – 130 °C [-40 – 266 °F]

View on TE.com >

Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance




Number of Positions: **94**

Primary Product Color: **Violet**

Connector & Contact Retention Accessory Type: **Retainer**

Primary Product Material: **PBT GF30**

Operating Temperature Range: **-40 – 130 °C [-40 – 266 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	Retainer

Configuration Features

Number of Positions	94

Body Features

Primary Product Color	Violet
Primary Product Material	PBT GF30

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2209545-1
94P,MQS CB,REC HSG,ASSY,SEALED


Customers Also Bought



TE Part #6-1355135-1
VERRIEGLUNG F.94P



TE Part #5-1418760-2
MCON 1.2 LL TAB STC AU




TE Part #5-1534116-2
MQS0,63 AU REC CB UNSEAL. 0,25-0,35 2P



TE Part #2112669-1
23POS MIXED MQS REC



TE Part #2112674-1
37POS MIXED MQS REC COD A



TE Part #2112674-2
37POS MIXED MQS REC COD B



TE Part #2112675-1
36POS MIXED MQS REC COD A



TE Part #2112675-2
36POS MIXED MQS REC COD B



TE Part #2137752-1
Lever for 154P ECU connector



TE Part #2209545-9
94P PLUG ASSY, NORMAL CODING

Documents

Product Drawings

VERRIEGLUNG F94P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1355134-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1355134-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1355134-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Modular Jack, Single or Dual Port, Surface Mount or Thru-Hole, Economy

English