




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 2150580-2
OCEAN_2.0_Applicator-E-110F150F-SEA




TE Part # 62131-8
CLSTR PIN RCPT




TE Part # 141101-2
RECEPT CLUSTER


Customers Also Bought




TE Part #62306-2
AMVAR SPLC 1500-5000 020TPBR




TE Part #62308-2
AMVAR SPLC 3000-7000 020TPBR




TE Part #63454-1
Cluster Block Recpt Amplivar 1500-4200



TE Part #170063-2
CLUSTER PIN REC




TE Part #316292-1
3.2 CLUSTER REC L-TYPE



TE Part #316293-1
3.2 CLUSTER BLOCK HSG NATURAL




TE Part #360052-1
125 DIA CLSTR BLK



TE Part #1123655-1
2.3 DIA CLUSTER AMPLIVER S TIN



TE Part #1744103-2
3.96 EPHDR ASSY 2P



TE Part #1-5533268-2
ASSY,RECPT,R.ANGLE,HDI,LEAD-FR

Documents

Product Drawings

2.3 CLUSTER REC AMPLIVAR TYPE

Japanese

CAD Files

Customer View Model

ENG_CVM_353937-1_E1.3d_igs.zip

English

Customer View Model



[ENG_CVM_353937-1_E1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_353937-1_E1.2d_dxf.zip](#)

English

3D PDF

3D

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_353937-1_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_353937-1_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_353937-1_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Application Specification

English