




MTA 156

TE Internal #: 3-644465-2
2 Position, Receptacle, Connector Assembly, Insulation
Displacement (IDC), Wire-to-Board, Tin (Sn), UL 94V-2, 3.96 mm [.156 in] Centerline, MTA 156

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Mating Alignment: **With**
Mating Alignment Type: **Polarizing Tab**
Connector & Housing Type: **Receptacle**
Mating Retention Type: **Locking Ramp**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1
Number of Power Positions	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Orange
-----------------------	--------



Cable Exit Angle	90°
Contact Features	
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	30 µm[.762 µin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
Wire Contact Termination Area Plating Thickness	2.03 – 5.08 µm[80 – 200 µin]
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A
Contact Type	Receptacle
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
Strain Relief	With
Panel Mount Feature	Without
Contact Retention Type Within Housing	Locking Lance
Mating Alignment	With
Mating Alignment Type	Polarizing Tab
Mating Retention Type	Locking Ramp
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Wire & Cable IDC Installation Type	Feed Through
Centerline (Pitch)	3.96 mm[.156 in]
Housing Material	Nylon
Dimensions	
Compatible Insulation Diameter Range	2.41 mm[.095 in]
Connector Height	9.78 mm[.385 in]



Connector Length	7.92 mm[.312 in]
Wire Size	.823 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	250
Packaging Method	Bag & Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 641533-1 02P MTA156 CONN HSG,END CAP	 TE Part # 644753-2 02P MTA156 HDR ASSY RN STR F/L	 TE Part # 640388-2 02P MTA156 HDR ASSY RN STR F/L	 TE Part # 2-647127-2 02P MTA156 SHRD HDR ASSY LF
 TE Part # 3-644617-2 02P MTA156 HDR ASY PO RA FB LF	 TE Part # 643067-2 02P MTA156 MOLDED COVER	 TE Part # 640631-3 MTA .156 CONTACT BRNBR	 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME
 TE Part # 644751-2 02P MTA156 HDR ASSY R/A	 TE Part # 640643-2 02P MTA156 COVER F/T	 TE Part # 644749-2 02P MTA156 HDR ASSY STR SQ SN	 TE Part # 2-647123-2 02P MTA156 SHRD HDR ASSY SQ SN
 TE Part # 640389-2 02P MTA156 HDR ASSY SQ R/A F/L	 TE Part # 640384-2 02P MTA156 HDR ASSY STR RND SN	 TE Part # 640551-2 02P MTA156 COVER	 TE Part # 640385-2 02P MTA156 HDR ASSY SQ R/A





TE Part # 640445-2
02P MTA156 HDR ASSY FL/STR SN



TE Part # 3-644611-2
02P MTA156 HDR POL WO PEGS LF



TE Part # 2-647125-2
02P MTA156 SHRD HDR ASSY LF



TE Part # 643071-2
02P MTA156 FD-THRU COVER


Also in the Series | MTA 156



Connector Caps & Covers(89)



Connector Contacts(4)



Connector Hardware(2)



Power Contacts(3)



Rectangular Power Connectors(1178)



Standard Rectangular Connectors(667)



Wire-to-Board Connector Assemblies & Housings(594)

Customers Also Bought




TE Part #GA10K3A1B
DISCRETE 10K OHMS, +/-0.2C FROM 0C TO 70C



TE Part #6-160430-6
187 FASTON REC 20-16 AWG BR



TE Part #2-1761713-3
IDC LOW PRO HDR 10P VERT SHT L




TE Part #1825615-1
BP1048004=Boot, Pushbutton



TE Part #9-1879336-1
CPF 0603 2K0 1% 50PPM 1K RL



TE Part #8-1879337-8
CPF 0603 20K 1% 50PPM 1K RL



TE Part #9-2176087-8
RP 1J 0.166W 715R 0.1% 25PPM 1K RL



TE Part #6609056-1
3MV1=F7756 S0



Documents

Product Drawings

02P MTA156 CONN ASSY 18AWG ORA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-644465-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-644465-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-644465-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

Agency Approval Document

English