

6-2287907-2 ✓ ACTIVE

AMP | FAKRA RF Connector System

TE Internal #: 6-2287907-2

Wire-to-Board, Edge, 1 Position, Board Mount, M Code, Signal, -40


- 105 °C [-40 – 221 °F], FAKRA RF Connector System, Data

Connectivity Headers

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Data Connectivity Headers



Connector System: **Wire-to-Board**

Sealable: **No**

Shielded: **No**

PCB Mount Orientation: **Edge**

Number of Positions: **1**

## Features

### Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Mixed & Hybrid Connector	No
Connector System	Wire-to-Board
Sealable	No

### Configuration Features

Number of Rows	1
PCB Mount Orientation	Edge
Number of Positions	1

### Electrical Characteristics

Operating Voltage	800 VAC
Impedance	50 Ω

### Body Features

PCB Retention Feature Plating Material	Tin
Body Material	PA GF



Connector & Keying Code	M
-------------------------	---

### Contact Features

Outer Contact Plating Material	Tin (Sn)
RF Connector Center Contact Plating Material	Gold (Au)
Contact Mating Area Plating Material	Gold (Au)
Center Contact	With
Contact Type	Pin
Mating Pin Diameter	.51 mm[.02 in]
Contact Current Rating (Max)	1 A

### Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

### Mechanical Attachment

Panel Attachment Style	Front Mount
PCB Mount Retention	With
Mating Retention	With
PCB Mount Retention Type	Solder Tail
Connector Mounting Type	Board Mount

### Housing Features

Housing Color	Pastel Orange
---------------	---------------

### Dimensions

Product Width	10 mm[.394 in]
Product Length	24.5 mm[.965 in]
Connector Height	8.4 mm[.33 in]

### Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

### Operation/Application

Operating Frequency Range	0 – 6 GHz
Shielded	No
Circuit Application	Signal

### Industry Standards



Compatible With Agency/Standards Products	SAE/USCAR-17
UL Flammability Rating	UL 94V-1, UL 94V-2

### Packaging Features

Packaging Quantity	1600
Packaging Method	Reel

### Other

Dielectric Material	PCT
---------------------	-----

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability






#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



## Also in the Series | FAKRA RF Connector System



## Customers Also Bought





## Documents

### Product Drawings

[FAKRA, 1 POS, EDGE MOUNT, 3 OCLOCK ASSY](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_6-2287907-2\\_E.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_6-2287907-2\\_E.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_6-2287907-2\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Application Specification](#)

English