382811-2 ✔ ACTIVE

AMP

TE Internal #: 382811-2

Economy Shunt, Open Top, 2 Position, 2.54 mm [.1 in] Centerline, Signal, -65 – 105 °C [-85 – 221 °F]

View on TE.com >

Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Jumpers & Shunts





Shunt Type: **Economy**

Shunt Style: **Open Top**

Number of Positions: **2**

Centerline (Pitch): **2.54 mm [.1 in]**

Contact Current Rating (Max): **3 A**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board

Configuration Features

Number of Positions	2

Electrical Characteristics

Insulation Resistance	1000 MΩ

Body Features

Primary Product Color	Blue
Handle	Without

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Thickness	.381 µm[15 µin]
Shunt Type	Economy

Shunt Style	Open Top
Contact Current Rating (Max)	3 A

Housing Features

Housing Material	Polyester GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Product Height	6.35 mm[.25 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Operation/Application

Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Packaging Features

Jumper & Shunt Packaging	Breakaway Strip of 10 Pieces
Packaging Method	Box
Packaging Quantity	1500

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 5-146276-2
02 MODII HDR SRST B/A .100CL




TE Part # 5-146280-2
02 MODII HDR SRST B/A .100CL



TE Part # 5-146284-2
02 MODII HDR SRST B/A .100CL


Customers Also Bought



TE Part #102536-1
06 AMPMODU MT COVER DR .100CL



TE Part #5-102694-1
06 ampmodu mt assy dr.sn



TE Part #1-825433-0
MOD 2 PINHDR 1X10P.



TE Part #1614782-8
BDS 2 A 100 220R 10%



TE Part #1614783-2
BDS 4 B 100 1R0 10%



TE Part #1877285-5
05P EP SHRD HDR ASMY, WHITE



TE Part #2108610-5
1.4H SPRING FINGER WITH EMBOSS



TE Part #3-2319847-3
END STACK DIP 2P J RAISED T&R



TE Part #5175472-1
CHAMP 050 BTB PLUG H W/LEG 20P



TE Part #6609037-2
3EP3=F7170 S0

Documents

Product Drawings

SHUNT, ECON, PHBR15 AU, BLUE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_382811-2_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_382811-2_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_382811-2_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Low Profile, Economy, and Dual Beam Shunt Connectors 382811, 390088, and 382823

English

Agency Approvals

Agency Approval Document

English