




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

MTA 156

Connector Caps & Covers(89)	Connector Contacts(4)	Connector Hardware(2)	Power Contacts(3)
Rectangular Power Connectors(1178)	Standard Rectangular Connectors(667)	Wire-to-Board Connector Assemblies & Housings(594)	

Customers Also Bought

TE Part #EC9833-000 ZHD-SCE-3.2-50-S1-4	TE Part #ASA158F12390235000 623 PLUG	TE Part #55992-1 TERMINAL,AMPOWER R 2/0 5/16	TE Part #1-1415543-5 RTE44110
TE Part #1614770-4 BDS 2 A 250 10R 10%	TE Part #ZPF000000000205373 PLUG MALE ANG.90 CAL.20 - FXP	TE Part #ZPF000000000136485 RECEPTACLE MALE FOR 12 PINS, CAL1,6	TE Part #ZPF000000000205378 CONTACT MALE ANG.90, CAL20, 120MM2 - FXP
TE Part #YZ-KC-212751A-PY00 TOOL DISMOUNTING - FXP2	TE Part #ZPF000000000205388 CONTACT FEMALE CAL.20, M12 - FXP		



Documents

Product Drawings

02P MTA156 CONN ASSY 18AWG ORA

English

CAD Files

Customer View Model

ENG_CVM_CVM_644465-2_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_644465-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_644465-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese