



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 13100 – 20800 CMA

Stud Size: #8, M4

Features

Product Type Features

Terminal Features	Sheared
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	3.413 g
----------------	---------

Contact Features

Barrel Type	Closed
Terminal Orientation	Flag
Terminal Plating Material	Nickel

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Wire Size	13100 – 20800 CMA
Stud Diameter	4.34 mm[.171 in]
Tongue Thickness	1.22 mm[.048 in]
Product Length	20.09 mm[.791 in]
Barrel Inside Diameter	4.57 mm[.18 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	0 – 343 °C[0 – 649 °F]

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1752681-2
HYP10 SOLIS FLAG 8AWG INDENTER



TE Part # 48506
HYP8 SOLIS FLAG 8AWG NEST



TE Part # 1752680-8
HYP10 SOLIS FLAG 8AWG NEST

Customers Also Bought



TE Part #35108
TERMINAL,PIDG R 12-10 8



TE Part #201330-1
CONTACT PIN ASSY.



TE Part #206043-1
RECEPT,SZ 17-14 CPC



TE Part #206070-8
CABLE CLAMP KIT #17




TE Part #206485-1
CPC PLUG ASSEMBLY SIZE 11-9



TE Part #321600
TERMINAL,SOLIS R 2 3/8



TE Part #350690-1
UMNL PIN 24-18 PTPBR L/P



TE Part #696724-1
STRATO-THERM, FLAG R 6 8 NIPL

TE Part #YCTL-20C0150000000
JUNCTION ASSY

Documents

Product Drawings
STRATO-THERM, FLAG R 8 8 NIPL



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_696722-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_696722-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_696722-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOLISTRAND - QRG

English