

TT41NGWW2T

✕ OBSOLETE

ALCOSWITCH

TE Internal #: 7-1437562-4

TE Internal Description: TT41NGWW2T=SW TOGGLE 4 POLE P/

[View on TE.com >](#)



Switches > Toggle Switches



Configuration (Pole-Throw): **Four Pole - Double Throw**

Operating Function: **On None On**

Contact Current Rating: **.4 A**

Operating Voltage: **20 VDC**

Product Orientation: **Vertical**

Features

Product Type Features

Sealed Device	Yes
Switch Connection Type	Wire Wrap
Toggle Style	Baton Medium
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Four Pole - Double Throw
Operating Function	On None On

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	1000 VAC
Insulation Resistance	1000 MΩ
Contact Current Rating	.4 A
Operating Voltage	20 VDC

Body Features

Case Color	Black
Product Orientation	Vertical
Bushing Style	Threaded
Bushing Thread Size	10-48

Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------



Switch Contact Plating Material

Gold over Nickel

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	7.37 mm[.29 in]
---------------	-----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought




TE Part #BTA3-28-13-4-J
[BTA3-28-13-4-J](#)



TE Part #BTA1-24-13-1-C
[BTA1-24-13-1-C](#)



TE Part #705557-000
[TXR21AB90-1406AI](#)



TE Part #579873-000
[MTCP-KT1-0009](#)



TE Part #ZPF000000000096565
[FDBA 57-14-5 PN-K 090 A838](#)



TE Part #ZPF000000000099321
[D-EASY 03 B 03](#)



TE Part #ZPF000000000100155
[FDBA 57-12-3 SN-K 090 A838](#)



TE Part #ZPF000000000095953
[FDBA 50-14-15 PN-K 090 A499](#)



TE Part #CV7478-000
[302A812-25-0](#)

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_7-1437562-4_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1437562-4_A1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1437562-4_A1.3d_igs.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English