



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**

Element Type: **Thick Film**

Package Size Code: **0603**

Power Rating: **.1 W**

Resistance Value: **536K  $\Omega$**

Features

Product Type Features

|                   |                |
|-------------------|----------------|
| Resistor Type     | Power Resistor |
| Element Type      | Thick Film     |
| Package Size Code | 0603           |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 50 V                      |
| Power Rating                | .1 W                      |
| Resistance Value            | 536K $\Omega$             |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Passive Component Tolerance | 1 %                       |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Surface Mount Resistor Termination Type | Solder |
| Number of Terminations                  | 2      |

Dimensions

|                |                 |
|----------------|-----------------|
| Product Height | .45 mm[.018 in] |
| Product Length | 1.6 mm[.063 in] |
| Product Width  | .8 mm[.031 in]  |



Usage Conditions

|                         |             |
|-------------------------|-------------|
| Temperature Coefficient | ±200 ppm/°C |
|-------------------------|-------------|

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Not Compliant                                                                                                                   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量超出标准 Restricted Substance(s) Above Threshold                                                                              |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUNE 2025 (250)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGV0603F536K

536K ohm, Thick Film, Power Resistor, 1 %, 0603, .1 W, ±200 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, NEOHM CRGV



TE Part # 3-1879530-4  
[CRGV1206 5% 2M4 1000V](#)

TE Part # 4-1879537-3  
[CRGV2010 1% 1M5 3000V](#)

TE Part # 2-1879532-0  
[CRGV2512 5% 330K 1600V](#)

TE Part # 3-1879530-3  
[CRGV1206 5% 2M2 1000V](#)

TE Part # 2-1879537-6  
[CRGV2010 1% 1M0 3000V](#)

Also in the Series | [NEOHM CRGV](#)

[Surface Mount Resistors\(992\)](#)

Customers Also Bought

TE Part #1-830611-0  
[LGH 1/2 SNGL MLD END](#)

TE Part #9-1625971-5  
[HSA25 R01 10%](#)

TE Part #1-1879353-9  
[RR02 5% 24K AMMO](#)


TE Part #7-1879354-5  
[RR03 5% 390R AMMO](#)

TE Part #7-1879648-1  
[H4P 287R 0.5% 100PPM](#)

TE Part #7-2176305-3  
[RP 1E 0.1W 604R 0.1% 25PPM 5K RL](#)

TE Part #3-2176307-2  
[RP 1E 0.1W 26K1 0.1% 25PPM 5K RL](#)

TE Part #2337238-3  
[TACT MINI GW 5.2X5.2X2 160GF](#)



Documents

Product Drawings

[CRGV0603 1% 536K 400V](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_7-1879533-1\\_BA.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_7-1879533-1\\_BA.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_7-1879533-1\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[High Voltage Thick Film Chip Resistors - Type CRGV series](#)

English