



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 521844-1 POWER BLOCK ASSEMBLY 16-12 AWG BR	 TE Part # 521843-1 POWER BLOCK ASSEMBLY 16-12 AWG PTPBR	 TE Part # 63166-5 POWER RING,TERMINAL 16-12 AWG PTPBR	 TE Part # 63166-4 POWER RING,TERMINAL 16-12 AWG BR
 TE Part # 1-1633966-1 CRIMPER,INSULATION O	 TE Part # 1803316-1 ANVIL, COMBINATION	 TE Part # 2151316-2 OCEAN_2.0_APPLICATOR-S-140F220O-SSA	 TE Part # 3-456411-0 CRIMPER, WIRE .140F PREMIUM

Customers Also Bought

 TE Part #CAT-D48-ST273 DEUTSCH Solid Contacts	 TE Part #DT04-2P REC, 2P, GRY, N	 TE Part #CAT-D487-W416 Wedgelocks: DEUTSCH DT	 TE Part #DT06-2S PLG, 2P, GRY, N
 TE Part #206070-8 CABLE CLAMP KIT #17	 TE Part #281934-2 SINGLE WIRE SEAL	 TE Part #CAT-AM71-CH8172 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	

Documents

Product Drawings
OCEAN_2.0_SPARE_PART_KIT-140F220O
English

Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION
English



Instruction Sheets

Instruction Sheet (U.S.)

English