




TE Internal #: 444025-1
Closed Ring Tongue Terminal, 11 – 9 AWG, #10 Stud, 8 mm [.314 in] Stud Diameter, Open Barrel, Straight, Unplated Plating, Uninsulated
[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**
Wire Size: **8233 – 13091 CMA**
Stud Size: **#10**

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Unplated

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	8233 – 13091 CMA
Stud Diameter	8 mm[.314 in]
Tongue Thickness	.6 mm[.023 in]
Product Length	26.2 mm[1.031 in]



Barrel Inside Diameter	2.9 mm, 3.8 mm[.114 in][.149 in]
Compatible Insulation Diameter (Max)	4.29 mm[.169 in]
Compatible Insulation Diameter Range	3.2 – 4.3 mm[.125 – .169 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	4000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides





on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 881000-1 RING TONGUE 2.5/4.0 MM2 BR	 TE Part # 444026-2 RT ANTI ROTATIONAL 1-5 MM2 ELECTRO TPBR	 TE Part # 626030-1 RING TONGUE 0.5 /1.5 MM2 BR	 TE Part # 444024-4 RING TONGUE ANTIROT.
 TE Part # 880642-3 RING TONGUE	 TE Part # 626279-1 RING TONGUE 0.5-1.50 MM2 PLAINNUBR	 TE Part # 444026-1 RING TONGUE ANTI ROTATIONAL 1- 5 MM2 BR	 TE Part # 626037-1 RING TONGUE TERMINAL 4.0-6.0 MM2 BR
 TE Part # 626034-1 RING TONGUE 1.0-2.5 MM2 .236 X . 521 BR	 TE Part # 880630-1 RING TONGUE	 TE Part # 881599-4 RINGUE TONGUE ANTIR	 TE Part # 626033-1 RING TONGUE 1.0-2.5 MM2 0.60 X 11.43 BR

Customers Also Bought

 TE Part #41589 SPADE TERMINAL 24-20 AWG TPBR	 TE Part #444026-1 RING TONGUE ANTI ROTATIONAL 1- 5 MM2 BR	 TE Part #521116-2 MOTOR HOUSING HOUSING NYLON VO BLACK	 TE Part #626279-1 RING TONGUE 0.5-1.50 MM2 PLAINNUBR
---	---	---	---



TE Part #626361-3
WALL PLUG PIN 0.5/1.5MM2 0.38X36.
40 NIBR

TE Part #735211-2
250 FASTON REC 14-10 AWG TPBR

TE Part #735212-1
FF 250 REC 22-17AWG BR

TE Part #881623-9
187 FASTON REC 20-17 AWG TPBR

TE Part #1-2133346-0
250 FASTON HSG.,REC.,1 POS,
NATRUAL

TE Part #1989915-1
250 FASTON HSG.,FLAG,REC.,1 POS,
NATRUAL

Documents

Product Drawings
RING TONGUE ANTITOR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_444025-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_444025-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_444025-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English