448816-3 ✔ ACTIVE

AMPLIMITE

TE Internal #: 448816-3

25 Position D-Shaped Connector, Receptacle, Cable-to-Cable, Panel Mount, Shell Size 3, 2.77 mm [.109 in] Centerline, Wire & Cable, Signal

View on TE.com >

Connectors > D-Shaped Connectors



Number of Positions: **25**

Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Cable**

Connector Mounting Type: **Panel Mount**

Connector Shell Size: **3**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
Connector Shell Size	3
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	25
Power/Signal/Coax Combination	No

Body Features

Front Shell Material	Brass
Mating Retention Feature Material	Copper Alloy
D-Sub Connector Insert Arrangement	MS18275-1
Rear Shell Plating Material	Gold
Rear Shell Material	Brass
Front Shell Plating Material	Gold

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy

Contact Type	Socket
Contact Size	Size 20
Contact Current Rating (Max)	7.5 A
Contact Options	Order Separately

Termination Features

Termination Method to Wire & Cable	Crimp

Mechanical Attachment

Mounting Hole Diameter	3.18 mm[.125 in]
Connector Mounting Type	Panel Mount
Mating Alignment	Without

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Signal

Packaging Features

Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (4% in Contact/Component) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 91067-2
INSERTION/EXTRACTION TOOL



TE Part # 206793-1
SZ 20,SOCKET, NON-MAG

Customers Also Bought



TE Part #E23232N001
SO63-1-W3-28-9CS2633

TE Part #338723-000
55/0312-22-9CS2570

Documents

Product Drawings

AMPLIMITE,ASY,RCPT,109,NM,CS,3

English

CAD Files

3D PDF

3D

Customer View Model
ENG_CVM_CVM_448816-3_K.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_448816-3_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_448816-3_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.