



MCON | MCON 1.2mm

TE Internal #: 5-1418760-1

Tab Terminal, 20 – 18 AWG, .5 – .75 mm² Wire, 1.15 mm [.045 in]

Tab Width, Tin (Sn), .6 mm [.024 in] Tab Thickness, Unsealed,

MCON 1.2mm

[View on TE.com >](#)

Automotive Parts > Automotive Terminals > MCON Receptacle and Tab



Terminal Type: **Tab**

Wire Size: **20 – 18 AWG**

Mating Tab Width: **1.15 mm [.045 in]**

Interface Plating: **Tin (Sn)**

[All MCON Receptacle and Tab \(63\)](#)

Features

Product Type Features

Receptacle Style	180°
Primary Locking Feature	Locking Lance
Sealable	No

Body Features

Terminal Seal Type	Unsealed
--------------------	----------

Contact Features

Crimp Type	F-Crimp
Contact Size	1.2mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Terminal Type	Tab
Mating Tab Width	1.15 mm[.045 in]
Interface Plating	Tin (Sn)



Mating Tab Thickness	.6 mm[.024 in]
----------------------	----------------

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.4 – 1.9 mm[.055 – .075 in]
Wire Size	20 – 18 AWG
Wire Size Search	.5 mm², .6 mm², .75 mm²
Tab Length	25.6 mm[1 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Conforms to Automation Guideline	Yes, DIN 72036 Automation of Wiring Harness Production, Version June 2024, Yes, KOMAX Guideline for automatic component insertion for electrical connections, Version 5.0 (March 2018)

Industry Standards

Compatible With Agency/Standards Products	LV214
---	-------

Packaging Features

Packaging Method	Reel
Packaging Quantity	9000

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold






EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-LMPH9507 Low & Medium Power Header	 TE Part # 2151300-2 OCEAN_2.0_APPLICATOR-S-055F072SP-RSA	 TE Part # 1-2236046-0 32W, MIXED, MALE CONN.,CLIP2, COD A, CPA	 TE Part # 2382878-4 3POS,1.2X0.63,TAB HSG,UNSLD,COD D
 TE Part # 2366066-6 48POS,MCON 1.2,TAB HSG ASSY, UNSLD,COD F	 TE Part # 5-1579007-3 EXTRACTION TOOL	 TE Part # 7-1452656-1 MCON 1.2 LL REC SRC SN	 TE Part # 2320771-1 HVP800 HEADER



TE Part # 2366066-2
48POS,MCON 1.2,TAB HSG ASSY,
UNSLD,COD B

TE Part # 2484266-1
33POS,HYBRID,TAB HSG ASSY,
UNSLD,COD A

TE Part # 2236046-8
32POS, MIXED, MALE CONN., CLIP2,
COD B

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No
Crimp

TE Part # 2382874-2
16POS,1.2X0.63,TAB HSG ASSY,
UNSLD,COD B

TE Part # 2366066-5
48POS,MCON 1.2,TAB HSG ASSY,
UNSLD,COD E

TE Part # 7-4151005-7
TOOLING KIT TO MAKE LOOSE
PIECE TERMINAL

TE Part # 4151005-1
APPLICATOR TO MAKE LOOSE
PIECE-RSM

TE Part # 2151300-1
OCEAN_2.0 APPLICATOR-S-
055F072SP-RSM

TE Part # 2236046-7
32POS, MIXED, MALE CONN., CLIP2,
COD A

TE Part # 2382878-1
3POS,1.2X0.63,TAB HSG,UNSLD,COD
A

TE Part # 2382874-1
16POS,1.2X0.63,TAB HSG ASSY,
UNSLD,COD A

Also in the Series | MCON 1.2mm

Automotive Connector Locks &
Position Assurance(9)

Automotive Housings(352)

Automotive Seals & Cavity Plugs(16)

Automotive Signal & Power Connector
Housings(348)

Other Automotive Connector
Accessories(12)

Customers Also Bought



TE Part #964265-2
TAB A 1.6x0.6 CONTACT CF SRC Sn

TE Part #1-969489-2
6POS MQS REC COD A

TE Part #5-1393292-8
V23074A2001A402-EV-CBOX

TE Part #1418762-1
MCON 1.2 LL TAB STC SN

TE Part #1418789-1
8POS MQS REC

TE Part #2236046-7
32POS, MIXED, MALE CONN., CLIP2, COD A

TE Part #1-2292507-1
CONNECTOR,TE,COVER 60 POSITION,ASSY

TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

Documents

Product Drawings
MCON 1.2 LL TAB STC SN

English

CAD Files
Customer View Model
ENG_CVM_CVM_5-1418760-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_5-1418760-1_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_5-1418760-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification

German

Application Specification

English

Application Specification

English